

# FL WLAN 5100 - Wireless module



2700718

<https://www.phoenixcontact.com/us/products/2700718>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



WLAN access point, client, WLAN 802.11 a, b, g, n, frequency 2.4 GHz, 5 GHz, IP20, connections: COMBICON for 10 ... 36 V DC, 2x RJ45 for LAN, central cluster management, WBM, 802.11i

## Commercial data

Item number	2700718
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN26
Product key	DNN2W4
GTIN	4046356625395
Weight per piece (including packing)	540.3 g
Weight per piece (excluding packing)	540.3 g
Customs tariff number	85176200
Country of origin	DE

## Technical data

### Notes

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---------------------------------------------------------------------------

### Product properties

Product type	Wireless module
Type	Stand-alone

#### Insulation characteristics

Pollution degree	2
------------------	---

#### Wireless card

Number	1
Type	IEEE 802.11 a/b/g/n 2.4 GHz and 5 GHz to 300 Mbps
Assembly note	Permanently installed

### Electrical properties

Maximum power dissipation for nominal condition	4.8 W
-------------------------------------------------	-------

#### Supply: Module electronics

Connection method	Via COMBICON
Supply voltage	24 V DC
Supply voltage range	10 V DC ... 36 V DC
Supply current	200 mA

### Interfaces

#### Ethernet

Interface	Ethernet
Number	2
Connection method	RJ45 jack

#### Antenna

Number	3
--------	---

#### Functions

Operating modes	Access point/client adapter/repeater/WDS bridge
Basic functions	SNMP (V2/V3), CLI, WPS, DHCP, DCP, BootP, HTTP, HTTPS, Syslog, SD card, dual FW image, 1 x DI, 1 x DO, 2 x Ethernet 10/100 Mbit, auto crossover, auto negotiation, MODE button
Configuration	Cluster management, web-based management, WPS
Automatic channel selection	yes
Security	802.11i WPA PSK (preshared key)

# FL WLAN 5100 - Wireless module



2700718

<https://www.phoenixcontact.com/us/products/2700718>

	WPA2
	AES
	TKIP
	Supports 802.1X/RADIUS
	MAC filter
Wireless licenses	EU, more countries in e-shop
Country support	Belgium
	Bulgaria
	China
	Denmark
	Germany
	Estonia
	Finland
	France
	Greece
	Great Britain
	Ireland
	Iceland
	Italy
	Qatar
	Latvia
	Liechtenstein
	Lithuania
	Luxembourg
	Malta
	Morocco
	Netherlands
	Norway
	Austria
	Poland
	Portugal
	Romania
	Sweden
	Switzerland
	Slovakia
	Slovenia
	Spain
	South Korea
	Taiwan
	Czech Republic
	Hungary
	Cyprus (rep.)

Ethernet (RJ45)

# FL WLAN 5100 - Wireless module



2700718

<https://www.phoenixcontact.com/us/products/2700718>

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Copper
Transmission length	100 m (per segment)
Signal LEDs	Data receive, link status
No. of channels	2 (RJ45 ports)

## Wireless

Designation	Wireless LAN
Antenna connection method	RSMA (female)
Number	3
Frequency band	2.4 GHz 5 GHz
Wireless standard	WLAN IEEE 802.11 a b g n
Transmission power	max. 23 dBm
Number of wireless interfaces	1 IEEE 802.11 a/b/g/n

## Dimensions

Width	40 mm
Height	109 mm
Depth	109 mm
Note on dimensions	Height with antenna socket, without antenna cable

## Material specifications

Color	silver gray
-------	-------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C (extended temperature range on request)
Air pressure (operation)	800 hPa ... 1080 hPa (up to 2000 m above sea level)
Air pressure (storage/transport)	660 hPa ... 1080 hPa (up to 3500 m above sea level)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

## Approvals

### Conformity/Approvals

# FL WLAN 5100 - Wireless module



2700718

<https://www.phoenixcontact.com/us/products/2700718>

ATEX	⊗ II 3 G Ex nA nC IIC T4 Gc X (Please follow the special installation instructions in the documentation!)
------	-----------------------------------------------------------------------------------------------------------

## Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

## Mounting

Mounting type	DIN rail mounting
Assembly note	Antennas not included in scope of supply

# FL WLAN 5100 - Wireless module



2700718

<https://www.phoenixcontact.com/us/products/2700718>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a)-I, 6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)