

TPS-1 EVA BOARD - Evaluation Board




2700881

<https://www.phoenixcontact.com/us/products/2700881>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Demo board for the TPS-1 PROFINET protocol chip



Product description

Test PROFINET communication with the TPS-1 EVA BOARD.
You can program demonstration applications using the LEDs provided.

Your advantages

- TPS-1 protocol chip
- PROFINET conformance class C
- LED diagnostics and status indicators

Commercial data

Item number	2700881
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR14
Product key	DRECBA
GTIN	4046356655385
Weight per piece (including packing)	194.7 g
Weight per piece (excluding packing)	194.7 g
Customs tariff number	85389091
Country of origin	DE

TPS-1 EVA BOARD - Evaluation Board

2700881

<https://www.phoenixcontact.com/us/products/2700881>




Set consists of

TPS-1 EVA BOARD - Evaluation Board

2700881

<https://www.phoenixcontact.com/us/products/2700881>

Demo board for the TPS-1 PROFINET protocol chip



TPS-1 EVA BOARD - Evaluation Board



2700881

<https://www.phoenixcontact.com/us/products/2700881>

Technical data

Product properties

Product type	Evaluation board
--------------	------------------

System properties

Module

Protocol chip	TPS-1
---------------	-------

Electrical properties

IC power supply voltage	5 V DC \pm 10 % (DC)
-------------------------	------------------------

Supply

Max. current consumption	200 mA (+7 mA per set LED)
--------------------------	----------------------------

Interfaces

Ethernet 10Base-T/100Base-TX

Bus system	RJ45
Connection method	RJ45 jack
Note on the connection method	2x
Transmission speed	10/100 Mbps (acc. to PROFINET standard)
Transmission physics	Twisted pair connection

Dimensions

Width	79 mm
Height	48 mm
Length	128 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	5 °C ... 55 °C
---------------------------------	----------------

TPS-1 EVA BOARD - Evaluation Board



2700881

<https://www.phoenixcontact.com/us/products/2700881>

Classifications

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

TPS-1 EVA BOARD - Evaluation Board



2700881

<https://www.phoenixcontact.com/us/products/2700881>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com