


# IB IL RS UNI-PAC - Communication module



2700893

<https://www.phoenixcontact.com/us/products/2700893>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline, Communication module, Serial data transmission; interface: RS-232, RS-485, RS-422: 1 (be operated simultaneously); Transmission speed: 110 bps ... 250000 bps; transmission speed in the local bus: 500 kbps; degree of protection: IP20; Scope of supply: including Inline connectors and marking fields

## Product description

The terminal is designed for use within an Inline station. It is used to operate standard I/O devices with serial interfaces on a bus system.

## Your advantages


- A serial input and output channel in RS-232, RS-422, and RS-485 format
- Various protocols supported
- Transmission speed can be set up to 250000 bps
- Number of data bits, stop bits and parity can be set
- Parameterization via process data or PCP
- Process data width can be set via DIP switches: 7, 15 or 31 words

## Commercial data

Item number	2700893
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR01
Product key	DRI151
GTIN	4046356657129
Weight per piece (including packing)	159.9 g
Weight per piece (excluding packing)	135 g
Customs tariff number	85389099
Country of origin	DE

## Technical data

### Dimensions

Dimensional drawing	
Width	24.4 mm
Height	135 mm
Depth	71.5 mm

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

#### Utilization restriction

CCCex note	Use in potentially explosive areas is not permitted in China.
------------	---

### Material specifications

Color (Housing)	green (RAL 6021)
-----------------	------------------

### Interfaces

#### Inline local bus

Number of interfaces	2
Connection method	Inline data jumper
Transmission speed	500 kbps

#### RS-232, RS-485, RS-422

Number of interfaces	1 (be operated simultaneously)
Connection method	Spring-cage connection
Note on the connection method	Use shielded cables.
Transmission speed	110 bps ... 250000 bps (can be parameterized)
Transmission physics	Copper
Protocols supported	Transparent, end-to-end, XON/XOFF
Termination resistor	typ. 120 Ω (active, integrated)
Data bits	5 ... 8
Stop bits	1 or 2
Input buffer	4 kByte
Output buffer	1 kByte

### System properties

2700893

<https://www.phoenixcontact.com/us/products/2700893>

## Programming data (LocalbusSlave)

Length code (hex)	1F
ID code (dec.)	223
Length code (dec)	31
Process data channel	496 bit
Input address area	max. 62 Byte
Output address area	max. 62 Byte
Parameter channel (PCP)	2 Byte
Register length (bus)	max. 64 Byte

## Fieldbus data telegram

Required parameter data	23 Byte
Required configuration data	5 Byte

## Product properties

Product type	I/O component
Product family	Inline
Type	modular
Installation location	Control cabinet
Scope of supply	including Inline connectors and marking fields

## Insulation characteristics

Overvoltage category	II (IEC 60664-1, EN 60664-1)
Pollution degree	2 (IEC 60664-1, EN 60664-1)

## Electrical properties

Maximum power dissipation for nominal condition	1.3 W
---	-------

### Potentials: Communications power ( $U_L$ )

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 90 mA (all connections of the serial interface are short-circuited) typ. 78 mA

### Potentials: Main circuit supply ( $U_M$ )

Supply voltage	24 V DC (via voltage jumper)
Current draw	max. 25 mA typ. 15 mA

## Electrical isolation/isolation of the voltage ranges

Test voltage: Serial interface/7.5 V supply (bus logic)	500 V AC, 50 Hz, 1 min
Test voltage: Serial interface/24 V supply $U_M$	500 V AC, 50 Hz, 1 min
Test voltage: Serial interface/functional ground	500 V AC, 50 Hz, 1 min
Test voltage: 7.5 V supply (bus logic)/functional ground	500 V AC, 50 Hz, 1 min
Test voltage: 24 V supply ( $U_M$ )/functional ground	500 V AC, 50 Hz, 1 min

## Connection data

### Connection technology

Connection name	Inline connector
-----------------	------------------

### Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

## Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# IB IL RS UNI-PAC - Communication module



2700893

<https://www.phoenixcontact.com/us/products/2700893>


## Drawings

Dimensional drawing




## Dimensions

Connection diagram



Block diagram



Internal wiring of the terminal points

# IB IL RS UNI-PAC - Communication module



2700893

<https://www.phoenixcontact.com/us/products/2700893>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2700893>



**cULus Listed**

Approval ID: E140324



**cULus Listed**

Approval ID: E140324

2700893

<https://www.phoenixcontact.com/us/products/2700893>

## Classifications

### ECLASS

ECLASS-13.0	27242608
ECLASS-15.0	27242608

### ETIM

ETIM 10.0	EC001604
-----------	----------

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

2700893

<https://www.phoenixcontact.com/us/products/2700893>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	66df9a2f-4646-4382-b2e8-5a02b6534d93

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)