

# AXC 1050 - Controller

2700988

<https://www.phoenixcontact.com/us/products/2700988>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Axio control for direct open-loop control of Axioline I/Os. With 2 Ethernet interfaces and programming capabilities according to IEC 61131-3. Complete with connector connector and labeling field.

## Product description

The AXC 1050 modular small-scale controller for the Axioline I/O system is fast, robust, and easy, i.e., it is consistently designed for maximum performance, easy handling, and use in harsh industrial environments.

## Your advantages

- PROFINET controller for up to 16 devices and/or PROFINET device functionality
- Memory extendable by up to 2 GB via plug-in SD card
- Free engineering with PC Worx Express (IEC 61131-3)
- Modbus/TCP-Client
- Integrated FTP and HTML5 web server
- Numerous protocols supported such as: HTTP, FTP, SNTP, SNMP, SMTP, SQL, MySQL, etc.

## Commercial data

Item number	2700988
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR10
Product key	DRAAEA
GTIN	4046356731195
Weight per piece (including packing)	234.1 g
Weight per piece (excluding packing)	244 g
Customs tariff number	85371091
Country of origin	DE

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

### Product properties

Product type	Controller
Product family	Axiicontrol
Type	modular

#### Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

#### Display

Diagnostics display	no
---------------------	----

### System properties

Retentive data storage	48 kByte (NVRAM)
------------------------	------------------

#### IEC 61131 runtime system

Program memory	2 Mbyte
Data storage system	2 Mbyte
Number of control tasks	8

#### Axioline

Amount of process data	max. 8192 bit (per station)
	max. 4096 bit (Axioline F local bus (input))
	max. 4096 bit (Axioline F local bus (output))
Number of supported devices	max. 63 (per station)
Number of local bus devices that can be connected	max. 63 (observe current consumption)

#### INTERBUS-Master

Amount of process data (Axioline input/output data max.)	max. 8192 bit (per station)
Amount of process data (Axioline input data max.)	max. 4096 bit (Axioline F local bus (input))
Amount of process data (Axioline output data max.)	max. 4096 bit (Axioline F local bus (output))
Amount of process data	max. 32768 bit (internal Modbus /TCP client)

#### PROFINET

Device function	PROFINET controller, PROFINET device
Specification	Version 2.3
	min. 32 ms (16 devices)

# AXC 1050 - Controller



2700988

<https://www.phoenixcontact.com/us/products/2700988>

Update rate	min. 32 ms (8 devices)
	min. 16 ms (4 devices)
	min. 8 ms (2 devices)
	min. 4 ms (1 device)
Conformance Class	A
Number of supported devices	max. 16 (at PROFINET controller)
Supported functions	MRP
	MRP
Device ID	0093 <sub>hex</sub>
Vendor ID	00B0 <sub>hex</sub>

## Function

Diagnostics display	no
Redundancy function	yes
Note on redundancy function	applicative system redundancy possible
Safety function	no

## Programming data

Register length (master)	1482 Byte
--------------------------	-----------

## Functionality

Programming languages supported	Instruction list (IL)
	Symbolic flowchart (SFC)
	Ladder diagram (LD)
	Function block diagram (FBD)
	Structured text (ST)

## System requirements

Configuration tool	Config+ Version 1.01 or later
Diagnostics tool	DIAG+
Runtime system	eCLR
Application interface	OPC

## Electrical properties

Maximum power dissipation for nominal condition	3.2 W
---	-------

## Real-time clock

Realtime clock	yes
Description realtime clock	1.73 s/day = 20 ppm at 25 °C

## Potentials

Protective circuit	Surge protection of the supply voltage; electronic
	Polarity reversal protection of the supply voltage; electronic

Potentials: Communications power  $U_L$  feed-in (the supply of the Axioline F local bus  $U_{BUS}$  is generated from  $U_L$ )

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)

2700988

<https://www.phoenixcontact.com/us/products/2700988>

Current draw	max. 650 mA (with 2 A at $U_{Bus}$ for the I/Os and $U_L = 24\text{ V}$ )
Current consumption	typ. 100 mA (without I/Os and $U_L = 24\text{ V}$ )
Power consumption	max. 13.2 W (2.0 A on $U_{Bus}$ , $U_L = 24\text{ V}$ )

Potentials: Axioline F local bus supply ( $U_{Bus}$ )

Supply voltage	5 V DC (via bus base module)
Power supply unit	2 A

## Connection data

Connection method	Push-in connection
-------------------	--------------------

Axioline F connector

Connection method	Push-in connection
Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 16
Stripping length	8 mm

## Interfaces

Web server	yes
------------	-----

Axioline F local bus

Number of interfaces	1
Connection method	Bus base module
Transmission speed	100 Mbps

Ethernet

Bus system	RJ45
Number of interfaces	2
Connection method	RJ45 jack
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps (half or full duplex (automatic detection))
Transmission physics	Ethernet in RJ45 twisted pair
No. of channels	2

Service

Bus system	USB
Number of interfaces	1
Connection method	Micro USB type B
Transmission speed	max. 115.2 kbps
No. of channels	1


## Dimensions

# AXC 1050 - Controller

2700988

<https://www.phoenixcontact.com/us/products/2700988>



Dimensional drawing	
Width	45 mm
Height	126.1 mm
Depth	74 mm
Note on dimensions	The depth applies when a TH 35-7.5 DIN rail is used (in accordance with EN 60715).

## Material specifications

Color	gray (RAL 7042)
-------	-----------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C up to 2000 m above mean sea level -25 °C ... 55 °C up to 3000 m above mean sea level
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (according to DIN EN 61131-2, non-condensing, no ice formation)
Permissible humidity (storage/transport)	5 % ... 95 % (according to DIN EN 61131-2, non-condensing, no ice formation)
Shock (operation)	10g (Bump endurance test according to DIN EN 60068-2-27)
Vibration (operation)	5g
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	58 kPa ... 106 kPa (up to 4500 m above mean sea level)

## Approvals

### UL, USA/Canada

Identification	cULus
Certificate	E238705

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Conformance with EMC directives	Immunity test in accordance with EN IEC 61000-6-2 Electrostatic discharge (ESD) IEC 61000-4-2 Criterion B, $\pm 6$ kV contact discharge, $\pm 8$ kV air discharge Immunity test in accordance with EN IEC 61000-6-2 Electromagnetic fields IEC 61000-4-3 Criterion A, Field intensity: 10 V/m Immunity test in accordance with EN IEC 61000-6-2 Fast transients (burst) IEC 61000-4-4 Criterion B, $\pm 2$ kV

# AXC 1050 - Controller

2700988

<https://www.phoenixcontact.com/us/products/2700988>



	Immunity test in accordance with EN IEC 61000-6-2 Transient overvoltage (surge)IEC 61000-4-5 Criterion B; DC supply lines: $\pm 0.5$ kV/ $\pm 1.0$ kV (symmetrical/asymmetrical), fieldbus cable shielding: $\pm 1.0$ kV
	Immunity test in accordance with EN IEC 61000-6-2 Conducted interferenceIEC 61000-4-6 Criterion A, Test voltage 10 V
	Noise emission test in accordance with EN IEC 61000-6-3 Class B

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# AXC 1050 - Controller


2700988

<https://www.phoenixcontact.com/us/products/2700988>



## Drawings

Dimensional drawing



# AXC 1050 - Controller

2700988

<https://www.phoenixcontact.com/us/products/2700988>



## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2700988>



**DNV GL**

Approval ID: TAA00000DF



**LR**

Approval ID: LR2480202TA-02

**BSH**

Approval ID: 840

**ABS**

Approval ID: 23-2449604-PDA



**cULus Listed**

Approval ID: E238705



**cULus Listed**

Approval ID: E238705

# AXC 1050 - Controller

2700988

<https://www.phoenixcontact.com/us/products/2700988>



## Classifications

### ECLASS

ECLASS-13.0	27242207
ECLASS-15.0	27242207

### UNSPSC

UNSPSC 21.0	32151700
-------------	----------

# AXC 1050 - Controller



2700988

<https://www.phoenixcontact.com/us/products/2700988>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	1832c9e3-43ef-4e09-b03e-951014e0fc84

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)