

VL PPC 7015 COMAU 01 - Panel PC



2701028

<https://www.phoenixcontact.com/us/products/2701028>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



IPC with touch screen

Commercial data

Item number	2701028
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR12
Product key	DRBAAB
GTIN	4046356685160
Weight per piece (including packing)	6.8 kg
Weight per piece (excluding packing)	6.8 kg
Customs tariff number	84714100
Country of origin	TW

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Panel PC
--------------	----------

Computer data

Processor	Intel® Core™ i7-660UE 1.33 GHz (Discontinued)
Operating system	Windows® XP Pro
RAM	4 GB DDR3 SODIMM
Data storage system	2.5" SSD, 32 GB

Display

Display type	38.1 cm / 15"-TFT
Screen resolution	1024 x 768 Pixel(s) (XGA)
Touch technology	Resistive industrial touch screen
Color spectrum	16.2 million colors
Graphics card	On-board graphics chip (AGP)

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Supply voltage	24 V DC (typical)
Supply voltage range	19.2 V DC ... 28.8 V DC

Real-time clock

Realtime clock	Yes (battery-backed)
----------------	----------------------

Supply

Power supply unit	24 V DC
-------------------	---------

Interfaces

Interfaces	COM 1 (V.24 (RS-232)), 1x DVI-D, 1x VGA, 4x USB, 2x CompactFlash®
Monitor output	1x DVI-D
	1x VGA
Network	2x Ethernet (10/100/1000 Mbps), RJ45

Ethernet (RJ45)

Connection method	2x RJ45
-------------------	---------

Dimensions

VL PPC 7015 COMAU 01 - Panel PC



2701028

<https://www.phoenixcontact.com/us/products/2701028>

Width	410 mm
Height	309 mm
Depth	99 mm

Installation dimensions

Width / Height / Installation depth	386.6 mm / 285 mm /
-------------------------------------	---------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	5 °C ... 55 °C (Configuration options can affect the operating temperature. See user manual for details)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Shock	15g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

Mounting

Mounting type	Panel cutout
---------------	--------------

2701028

<https://www.phoenixcontact.com/us/products/2701028>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	15(a), 6(c), 7(a), 7(c)-I

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com