

# NLC-IO-06I-04QTP-01A - I/O extension module



2701072

<https://www.phoenixcontact.com/us/products/2701072>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



I/O extension module for use with Nanoline base unit. Equipped with 6 digital input and 4 PNP digital output channels. A maximum of three I/O extension modules can be attached to a base unit.

## Your advantages

- Automatically recognized by the firmware
- I/O modules are electrically isolated
- Up to 3 modules can be added to the right side of a base unit
- Can be powered from a secondary power supply

## Commercial data

Item number	2701072
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR11
Product key	DRACAB
GTIN	4046356325332
Weight per piece (including packing)	173.3 g
Weight per piece (excluding packing)	137.6 g
Customs tariff number	85389099
Country of origin	IN

## Technical data

### Product properties

Product type	Extension module
Product family	Nanoline
Mounting position	Attaches to DB-9 connector on right-side of base unit

### Electrical properties

#### Supply: Module electronics

Connection method	Screw connection
Supply voltage	24 V DC
Supply current	typ. 50 mA max. 90 mA

### Input data

#### Digital:

Input name	Digital inputs
Description of the input	PNP/NPN
Number of inputs	6
Connection method	Screw connection
Input voltage range "0" signal	0 V DC ... 5 V DC
Input voltage range "1" signal	15 V DC ... 30 V DC
Nominal input voltage $U_{IN}$	24 V DC
Nominal input current at $U_{IN}$	5 mA DC (On) < 100 $\mu$ A (Off)
Typical response time	60 $\mu$ s (on) 70 $\mu$ s (OFF)

### Output data

#### Digital:

Output name	Digital outputs
Output description	PNP outputs
Connection method	Screw connection
Number of outputs	4
Protective circuit	Short-circuit and overload protection
Maximum output current per channel	500 mA
Maximum output current per module / terminal block	2 A
Maximum output current per module	2 A
Nominal load, inductive	12 VA ((1.2H))
Nominal load, lamp	12 W
Nominal load, ohmic	12 W
Maximum operating frequency with ohmic nominal load	100 Hz

# NLC-IO-06I-04QTP-01A - I/O extension module




2701072

<https://www.phoenixcontact.com/us/products/2701072>

## Connection data

Connection method	Screw connection
-------------------	------------------

## Dimensions

Dimensional drawing	
Width	40 mm
Height	103.5 mm
Depth	43 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C
Degree of protection	IP20
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	0 % ... 90 %

## Mounting

Mounting type	DIN rail mounting
	DIN rail mounting
Mounting position	Attaches to DB-9 connector on right-side of base unit

# NLC-IO-06I-04QTP-01A - I/O extension module




2701072


<https://www.phoenixcontact.com/us/products/2701072>

## Drawings

Dimensional drawing



Connection diagram



# NLC-IO-06I-04QTP-01A - I/O extension module



2701072

<https://www.phoenixcontact.com/us/products/2701072>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2701072>



**UL Listed**

Approval ID: E238705



**cUL Listed**

Approval ID: E238705

2701072

<https://www.phoenixcontact.com/us/products/2701072>

## Classifications

### ECLASS

ECLASS-13.0

27242216

### ETIM

ETIM 9.0

EC001417

### UNSPSC

UNSPSC 21.0

39122300

2701072

<https://www.phoenixcontact.com/us/products/2701072>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	95c8bbfb-f003-45b3-a318-976d4e1ab4b8

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)