

NLC-MOD-RS485 - Option module



2701182

<https://www.phoenixcontact.com/us/products/2701182>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

RS-485 connection for data transfer or software configuration



Your advantages

- Password control can limit access: read-only or read/write
- Watchdog timer monitors communication, providing either a warning or fault
- All I/O points, registers, flags, timers, counters, and system flags can be read and written remotely and independently of the program. This enables Nanoline to be used as a simple Modbus I/O block.
- Serial modules provide a PC connection for configuration purposes and downloading/uploading projects to a basic unit

Commercial data

Item number	2701182
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR11
Product key	DRACAE
GTIN	4046356325394
Weight per piece (including packing)	38.9 g
Weight per piece (excluding packing)	34.6 g
Customs tariff number	85366990
Country of origin	IN

Technical data

Product properties

Product type	Communication module
--------------	----------------------

Electrical properties

Supply

Supply voltage	24 V DC (Power available via logic module)
I/O voltage	24 V
Max. current consumption	18 mA
Typical current consumption	10 mA

Connection data

Slot 1

Connection method	Installs in slot 1 of logic module
-------------------	------------------------------------

Interfaces

Stop bits	1 or 2
-----------	--------

Data

Serial transmission speed	115.2 kbps
Connection method	RJ11, shielded

RS-232

Connection method	RJ11, shielded
-------------------	----------------

Dimensions

Width	24.5 mm
Height	25.5 mm
Depth	49 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C

NLC-MOD-RS485 - Option module



2701182

<https://www.phoenixcontact.com/us/products/2701182>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2701182>



UL Listed

Approval ID: E238705



cUL Listed

Approval ID: E238705

NLC-MOD-RS485 - Option module



2701182

<https://www.phoenixcontact.com/us/products/2701182>

Classifications

ECLASS

ECLASS-13.0

27242216

ETIM

ETIM 9.0

EC001417

UNSPSC

UNSPSC 21.0

39122300

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com