

BL PPC12 1000 - Panel PC



2701336

<https://www.phoenixcontact.com/us/products/2701336>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



IP65-rated, fanless, 12-inch industrial panel PC (PPC) including resistive touch screen with LED backlight. Energy-efficient Intel® Atom™ processor with 2 GB RAM. Ready for installation of mass storage device.

Product description

The Basicline PPC12 1000 is a 12-inch panel PC with a vibrant LED backlit display. The Intel® Atom™ 1.66 GHz N455 processor offers a seamless balance of processing power and energy efficiency. A fanless design and rich I/O capability make the BL PPC 1000 an industrial panel PC that can be used in a wide variety of applications. The three built-in COM ports enable connection to legacy RS-232 devices. One COM port can also be configured for RS-422 or RS-485 protocols.

Your advantages

- Fanless design
- 3 COM ports
- Embedded operating system support only
- LCD display with resistive touch screen
- IP65 degree of protection (front) IP20 rating (back)
- Energy-efficient Intel® ATOM™ processors

Commercial data

Item number	2701336
Packing unit	2 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR12
Product key	DRBABB
GTIN	4046356773102
Weight per piece (including packing)	4,318 g
Weight per piece (excluding packing)	4,318 g
Customs tariff number	84714100
Country of origin	TW

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Panel PC
--------------	----------

Computer data

Processor	Intel® Atom™ N455 1.66 GHz
Operating system	without operating system
RAM	2 GB DDR3 SODIMM
Data storage system	without data storage
Cooling	passive
Slots	without slots
Optical drive	without drive

Display

Display type	30.7 cm / 12.1"-TFT
Screen resolution	800 x 600 Pixel(s) (SVGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	350 cd/m ² , typical (adjustable)
MTBF	> 50000 h
Color spectrum	16.2 million colors

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 28.8 V DC
Power supply unit	24 V DC ±20 %

Real-time clock

Realtime clock	Yes (battery-backed)
----------------	----------------------

Supply

Power consumption	typ. 12.5 W
-------------------	-------------

Connection data

Connection method	COMBICON
Conductor cross-section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 2.5 mm ²

BL PPC12 1000 - Panel PC



2701336

<https://www.phoenixcontact.com/us/products/2701336>

Conductor cross-section AWG	24 ... 12
-----------------------------	-----------

Interfaces

Interfaces	4x USB 2.0
	1x COM (RS-232/422/485)
	2x COM (RS-232)
Network	2x Ethernet (10/100/1000 Mbps), RJ45
LAN chipset	Realtek® 8111D PCI-E
Bus system	without bus system

Dimensions

Width	365 mm
Height	282 mm
Depth	55 mm

External dimensions

Width / Height / Depth	365 mm / 282 mm / 55 mm
------------------------	-------------------------

Installation dimensions

Width / Height / Installation depth	334 mm / 253 mm / (Installation cutout)
-------------------------------------	---

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Shock	15g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

Mounting

Mounting type	Panel cutout
---------------	--------------

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com