

ANT-DIR-5900-01 - Antenna

2701348

<https://www.phoenixcontact.com/us/products/2701348>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Directional antenna, 5 GHz, gain: 9 dBi, polarization: $\pm 45^\circ$ dual-slant, opening angle: h/v $70^\circ/60^\circ$, degree of protection: IP67, seawater-resistant, connection: 2 x N (female), incl. mounting bracket and mast clips



Your advantages

- Salt water resistant
- For large distances
- For stationary or linear mobile applications
- For point-to-point connections

Commercial data

Item number	2701348
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN23
Product key	DNN2Z1
GTIN	4046356739405
Weight per piece (including packing)	464.3 g
Weight per piece (excluding packing)	464.3 g
Customs tariff number	85177100
Country of origin	PL

2701348

<https://www.phoenixcontact.com/us/products/2701348>

Technical data

Product properties

Product type	Antenna
Gain	9 dBi
Vertical beamwidth	60 ° (at 5 GHz)
Horizontal beamwidth	70 ° (at 5 GHz)
Polarization	Linear vertical

Electrical properties


Frequency band	5 GHz
Frequency range	5.15 GHz ... 5.875 GHz
Impedance	50 Ω
Voltage standing wave ratio VSWR in a 50 Ω system	≤ 1.50

Connection data

Connection technology

Connection method	N (female)
Outside diameter	25 mm ... 85 mm (Mast)

Dimensions

Dimensional drawing	
Width	80 mm
Height	101 mm
Length	35 mm

External dimensions

Outside diameter	25 mm ... 85 mm (Mast)
------------------	------------------------

Material specifications

Material	Lexan EXL 9330
	V2A
	V2A

Cable/line

Connecting cable	no
------------------	----

ANT-DIR-5900-01 - Antenna

2701348

<https://www.phoenixcontact.com/us/products/2701348>



Environmental and real-life conditions

Ambient conditions


Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C

Mounting

Mounting type	Panel mounting
	Mast mounting

Drawings

Dimensional drawing



Mounting panel


ANT-DIR-5900-01 - Antenna

2701348

<https://www.phoenixcontact.com/us/products/2701348>



Schematic diagram



Mounting panel


ANT-DIR-5900-01 - Antenna

2701348

<https://www.phoenixcontact.com/us/products/2701348>



Schematic diagram




Panel mounting

ANT-DIR-5900-01 - Antenna

2701348

<https://www.phoenixcontact.com/us/products/2701348>

Schematic diagram



Mast mounting


ANT-DIR-5900-01 - Antenna

2701348

<https://www.phoenixcontact.com/us/products/2701348>



Schematic diagram



Sealing tape available as an accessory


ANT-DIR-5900-01 - Antenna

2701348

<https://www.phoenixcontact.com/us/products/2701348>



Schematic diagram



Installation example

ANT-DIR-5900-01 - Antenna

2701348

<https://www.phoenixcontact.com/us/products/2701348>



Classifications

UNSPSC

UNSPSC 21.0	43221715
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------