

# RAD-ISM-2400-ANT-VAN-3-0-RSMA - Antenna



2701358

<https://www.phoenixcontact.com/us/products/2701358>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Omnidirectional antenna with protection against vandalism for control cabinet mounting, frequency band: 2.4 GHz, gain: 3 dBi, degree of protection: IP55, shockproof: IK08, connection: RSMA (male), incl. 1.5 m connecting cable

## Your advantages

- Ideally suited for freely mobile or stationary 2.4 GHz applications
- Impact-resistant housing (IK08)
- Including 1.5 m connecting cable

## Commercial data

Item number	2701358
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN23
Product key	DNN2Z1
GTIN	4046356741750
Weight per piece (including packing)	174.5 g
Weight per piece (excluding packing)	172 g
Customs tariff number	85177100
Country of origin	PL

# RAD-ISM-2400-ANT-VAN-3-0-RSMA - Antenna



2701358

<https://www.phoenixcontact.com/us/products/2701358>

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Antenna
Radiation characteristics	Omnidirectional
Gain	3 dBi
Vertical beamwidth	85 °
Horizontal beamwidth	360 °
Polarization	Linear vertical

### Electrical properties


Frequency band	2.4 GHz
Frequency range	2.4 GHz ... 2.5 GHz
Impedance	50 Ω
Maximum capacity	75.00 W
Voltage standing wave ratio VSWR in a 50 Ω system	≤ 1.50

### Connection data

#### Connection technology

Connection method	RSMA (male)
-------------------	-------------

### Dimensions

Dimensional drawing	
Height	43 mm
Diameter	86 mm

### Material specifications

Material	ASA Aluminum
Flammability rating according to UL 94	V0
Outer sheath, material	RADOX®(LSFH)

### Cable/line

Cable length	1.50 m
Connecting cable	yes

# RAD-ISM-2400-ANT-VAN-3-0-RSMA - Antenna



2701358

<https://www.phoenixcontact.com/us/products/2701358>

External cable diameter	3.20 mm
Outer sheath, material	RADOX®(LSFH)
Smallest bending radius, fixed installation	5 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP55
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Wind velocity	12.34568 km/h (Has a force of 10 N)

## Mounting

Mounting type	Control cabinet mounting
	Panel mounting
Assembly note	Optional panel mounting
	Outdoors and indoors

# RAD-ISM-2400-ANT-VAN-3-0-RSMA - Antenna




2701358

<https://www.phoenixcontact.com/us/products/2701358>

## Drawings

Dimensional drawing




# RAD-ISM-2400-ANT-VAN-3-0-RSMA - Antenna

2701358

<https://www.phoenixcontact.com/us/products/2701358>



Schematic diagram



Installation example


# RAD-ISM-2400-ANT-VAN-3-0-RSMA - Antenna



2701358

<https://www.phoenixcontact.com/us/products/2701358>

Drilling plan/solder pad geometry



# RAD-ISM-2400-ANT-VAN-3-0-RSMA - Antenna



2701358

<https://www.phoenixcontact.com/us/products/2701358>

## Classifications

### ECLASS

ECLASS-13.0	19070105
ECLASS-15.0	19070105

### ETIM

ETIM 10.0	EC001698
-----------	----------

### UNSPSC

UNSPSC 21.0	43223100
-------------	----------

2701358

<https://www.phoenixcontact.com/us/products/2701358>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	0f7eaaaa-0daa-4cfe-8a11-c986ba41a396

### EF3.1 Climate Change

CO2e kg	9.717 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)