

# PSI-DATA/BASIC-MODEM/RS232 - Modem



2313067

<https://www.phoenixcontact.com/us/products/2313067>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Industrial analog modem for assembly on EN DIN rails. Worldwide access to industrial PCs, machines and systems. Serial RS-232 interface, 3-way electrical isolation, supply voltage 24 V DC.

## Your advantages

- Configurable, selective call acceptance
- High-quality electrical isolation
- Connection establishment with password protection
- Integrated surge protection to ensure high system availability
- Callback function

## Commercial data

Item number	2313067
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN24
Product key	DNC411
GTIN	4046356098823
Weight per piece (including packing)	228.1 g
Weight per piece (excluding packing)	117.8 g
Customs tariff number	85176200
Country of origin	DE

## Technical data

### Notes

#### Utilization restriction

CCCex note	Use in potentially explosive areas is not permitted in China.
------------	---

### Product properties

Product type	Modem
MTTF	628 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	290 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%)
	115 Years (SN 29500 standard, temperature 40°C, operating cycle 100%)

### Electrical properties

Electrical isolation	VCC // PSTN // V.24 (RS-232)
Maximum power dissipation for nominal condition	2.4 W
Mains type	Fixed-line network
Test voltage data interface/power supply	1.5 kV <sub>rms</sub> (50 Hz, 1 min.)
Test voltage data interfaces	1500 V

#### Supply

Supply voltage range	10 V DC ... 30 V DC (via pluggable COMBICON screw terminal block)
Nominal supply voltage	24 V DC ±5 % (as an alternative or redundant, via backplane bus contact and system current supply)
Typical current consumption	< 100 mA (24 V DC)
	< 40 mA

### Connection data

#### Supply

Tightening torque	0.56 Nm ... 0.79 Nm
-------------------	---------------------

### Interfaces

Signal	RS-232
--------	--------

Data: V.24 (RS-232) interface in acc. with ITU-T V.28, EIA/TIA-232, DIN 66259-1

Serial transmission speed	0.3; 1.2; 2.4; 4.8; 9.6; 19.2; 38.4; 57.6; 115.2 kbps
Connection method	D-SUB 9 plug
Transmission length	15 m
File format/coding	Serial asynchronous UART/NRZ, 7/8 data, 1/2 stop, 1 parity, 10/11-bit character length
Data flow control/protocols	Software handshake, Xon/Xoff or hardware handshake RTS/CTS

Data: PSTN-Port (a/b-Line)

2313067

<https://www.phoenixcontact.com/us/products/2313067>

Connection method	RJ12, 6-pos.
Dialing procedure	Multiple frequency/pulse dialing, configuration via software

## Dimensions

Width	22.5 mm
Height	99 mm
Depth	114.5 mm

## Material specifications

Material (Housing)	PA V0
--------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 55 °C

## Approvals

### Corrosive gas test

Identification	ISA-S71.04-1985 G3 Harsh Group A
----------------	----------------------------------

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise immunity	EN 61000-6-2:2005

### Noise emission

Standards/regulations	EN 55032
-----------------------	----------

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# PSI-DATA/BASIC-MODEM/RS232 - Modem



2313067

<https://www.phoenixcontact.com/us/products/2313067>

## Classifications

### UNSPSC

UNSPSC 21.0	43222600
-------------	----------

2313067

<https://www.phoenixcontact.com/us/products/2313067>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)