

PSI-WL-PLUG-USB/BT - USB Bluetooth adapter



2313083

<https://www.phoenixcontact.com/us/products/2313083>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bluetooth-USB adapter for direct assembly on USB type A ports and wireless transmission from USB interfaces

Commercial data

Item number	2313083
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DNC661
GTIN	4046356098830
Weight per piece (including packing)	146.3 g
Weight per piece (excluding packing)	146.3 g
Customs tariff number	85176200
Country of origin	TW

2313083

<https://www.phoenixcontact.com/us/products/2313083>

Technical data

Product properties

Product type	Adapter
Application	USB/Bluetooth

Electrical properties

Supply

Nominal supply voltage	5 V DC (Directly via the USB interface)
Typical current consumption	100 mA (5 V DC)

Connection data

Supply

Tightening torque	0.56 Nm ... 0.79 Nm
-------------------	---------------------

Interfaces

Data: USB 2.0

Serial transmission speed	Up to 2.1 Mbps
Connection method	USB type A, male connector
Transmission length	max. 5 m
File format/coding	Synchronous / asynchronous
Data flow control/protocols	Transparent to protocol incl. 3964 R protocol

Wireless

Interface description	Bluetooth 2.0
Frequency range	2.402 GHz ... 2.48 GHz (ISM bandwidth)
Transmission method	1.6 kHz (FHSS)
Transmit capacity, minimum	20 dBm
Minimum receiver sensitivity	-80 dBm
Antenna	Internal
Range	20 dBm (100 mW) = 80 m ... 150 m

Dimensions

Width	18 mm
Height	58 mm
Depth	8 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 70 °C
Altitude	≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation)

PSI-WL-PLUG-USB/BT - USB Bluetooth adapter



2313083

<https://www.phoenixcontact.com/us/products/2313083>

EMC data

Electromagnetic compatibility	Conformance with R&TTE directive 1999/5/EC
Noise immunity	Not relevant, cable length < 3 m

Noise emission

Standards/regulations	EN 55022 / Class B
-----------------------	--------------------


PSI-WL-PLUG-USB/BT - USB Bluetooth adapter

2313083

<https://www.phoenixcontact.com/us/products/2313083>

Drawings

Functional drawing



PSI-WL-PLUG-USB/BT - USB Bluetooth adapter



2313083

<https://www.phoenixcontact.com/us/products/2313083>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com