

# FB-2SP-ET - Device coupler

2316022

<https://www.phoenixcontact.com/us/products/2316022>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device coupler for Foundation Fieldbus and PROFIBUS PA with Trunk In and Trunk Out connections (preinstalled mechanical terminator) and additional terminal connections for 2 spurs connected to fieldbus end devices.

## Your advantages

- Power is supplied to the device couplers via the TBUS
- The TBUS routes the fieldbus data from the trunk line modules to the extension modules
- Recommended for high-density control cabinet installations
- LEDs indicate the power and error state
- Built-in short-circuit protection

## Commercial data

Item number	2316022
Packing unit	1 pc
Sales key	DN11
Product key	DNC144
GTIN	4046356298704
Weight per piece (including packing)	103.1 g
Weight per piece (excluding packing)	94.4 g
Customs tariff number	85176200
Country of origin	SG

## Technical data

### Product properties

Product type	Device coupler
--------------	----------------

### Electrical properties

#### Supply

Supply voltage range	9 V DC ... 31 V DC (input on trunk line side)
Typical current consumption	7 mA

### Ex data

#### Safety data

Max. external inductivity $L_o$ / Max. external capacitance $C_o$	0.25 mH / 60 nF
---	-----------------

### Interfaces

#### Data: Foundation Fieldbus and PROFIBUS PA Segment

Connection method	Pluggable COMBICON screw connection for each spur
Termination resistor	100 $\Omega$ , external removable plug included
Conductor cross-section flexible max.	2.5 mm <sup>2</sup>
Conductor cross-section flexible min.	0.2 mm <sup>2</sup>
Conductor cross-section, rigid max.	2.5 mm <sup>2</sup>
Conductor cross-section, rigid min.	0.2 mm <sup>2</sup>
Conductor cross-section AWG max.	12
Conductor cross-section AWG min.	24
Output nominal voltage	$\leq 31$ V (per spur)
Output current	$\leq 43$ mA (per spur)
Maximum output current	$\leq 58$ mA (per spur)
Surge protection	Active if voltage exceeds 39 V (typ.) or 41 V (max.)
Voltage drop trunk line / outputs	$\leq 1.3$ V

#### Data: Foundation Fieldbus and PROFIBUS PA

Connection method	Pluggable screw connection
Conductor cross-section flexible max.	2.5 mm <sup>2</sup>
Conductor cross-section flexible min.	0.2 mm <sup>2</sup>
Conductor cross-section, rigid max.	2.5 mm <sup>2</sup>
Conductor cross-section, rigid min.	0.2 mm <sup>2</sup>
Conductor cross-section AWG max.	12
Conductor cross-section AWG min.	24

### Signaling


Status display	LED (green = Power OK; yellow = trunk comms OK; red = spur short-circuit)
----------------	---

# FB-2SP-ET - Device coupler

2316022

<https://www.phoenixcontact.com/us/products/2316022>

## Dimensions

Dimensional drawing	
Width	17.5 mm
Height	98.4 mm
Depth	70.4 mm

## Material specifications

Color	green
-------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Max. permissible relative humidity (operation)	95 % (non-condensing)
Shock	15g, 11 ms
Vibration (operation)	10 Hz ... 150 Hz, 1g

## Approvals

### Conformity/Approvals

ATEX	⊕ II 3 G Ex nA [nL] IIC T4 X
IEC	IEC 60529, IEC 61158-2
UL, USA / Canada	Class I, Zone 2, Group IIC T4 Class I, Div. 2, Groups A, B, C, D, T4
EN	EN 61326, EN 60068-2-27, EN 60068-2-6
NE	NAMUR NE 21

## Standards and regulations

### Standards

Standards/regulations	IEC 60529, IEC 61158-2
	NE21
	EN 61326, EN 60068-2-27, EN 60068-2-6

## Mounting

Mounting type	DIN rail mounting
Mounting position	horizontal DIN rail NS 35, EN 60715


# FB-2SP-ET - Device coupler

2316022


<https://www.phoenixcontact.com/us/products/2316022>

## Drawings

Dimensional drawing



Circuit diagram



Connection diagram: FB-2SP-ET

# FB-2SP-ET - Device coupler

2316022

<https://www.phoenixcontact.com/us/products/2316022>



## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)