

# FB-PA/SC - Repeater

2316375

<https://www.phoenixcontact.com/us/products/2316375>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

PROFIBUS PA interface module with oscilloscope



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2316375       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DN11          |
| Product key                          | DNC135        |
| GTIN                                 | 4055626021515 |
| Weight per piece (including packing) | 311.3 g       |
| Weight per piece (excluding packing) | 281 g         |
| Customs tariff number                | 85176200      |
| Country of origin                    | NL            |

## Technical data

### Notes

#### Note on application

|                     |                         |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

### Product properties

|              |                |
|--------------|----------------|
| Product type | Device coupler |
|--------------|----------------|

### Electrical properties

#### Supply

|                          |                        |
|--------------------------|------------------------|
| Supply voltage range     | Supplied via backplane |
| Max. current consumption | 12 mA                  |

### Connection data

#### Supply

|                                   |   |
|-----------------------------------|---|
| Connection method                 | Bus base module                               |
| Conductor cross-section, flexible | 0.20 mm <sup>2</sup> ... 2.50 mm <sup>2</sup> |
| Conductor cross-section, rigid    | 0.20 mm <sup>2</sup> ... 2.50 mm <sup>2</sup> |
| Conductor cross-section AWG       | 24 ... 12                                     |

### Dimensions

|        |        |
|--------|--------|
| Width  | 25 mm  |
| Height | 100 mm |
| Depth  | 132 mm |

### Material specifications

|       |       |
|-------|-------|
| Color | green |
|-------|-------|

### Environmental and real-life conditions

#### Ambient conditions

|  |                               |
|--|-------------------------------|
| Degree of protection                     | IP20                          |
| Ambient temperature (operation)          | -20 °C ... 60 °C              |
| Ambient temperature (storage/transport)  | -20 °C ... 60 °C              |
| Altitude                                 | 2000 m                        |
| Permissible humidity (operation)         | 5 % ... 95 % (non-condensing) |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing) |

### Approvals

#### Conformity/Approvals

|                  |                   |
|------------------|-------------------|
| UL, USA / Canada | UL 508 Listed     |
| UL, Canada       | CSA C22.2 No. 142 |

## Standards and regulations

### Standards/regulations

|                       |  |
|-----------------------|--|
| Standards/regulations | Ring wave noise immunity in acc. with IEC 61000-4-12 |
|-----------------------|--|

### Standards/regulations

|                       |                                   |
|-----------------------|-----------------------------------|
| Standards/regulations | Dry heat in acc. with IEC 61131-2 |
|-----------------------|-----------------------------------|

### Standards/regulations

|                       |                                    |
|-----------------------|------------------------------------|
| Standards/regulations | Damp heat in acc. with IEC 61131-2 |
|-----------------------|------------------------------------|

### Standards/regulations

|                       |  |
|-----------------------|--|
| Standards/regulations | Shock and vibration in acc. with EN 61131-2 and EN 50178 |
|-----------------------|--|

### PROFIBUS standardization

|                       |             |
|-----------------------|-------------|
| Standards/regulations | IEC 61158-2 |
|-----------------------|-------------|

## Mounting

|                   |  |
|-------------------|--|
| Mounting type     | DIN rail: 35 mm                                    |
| Mounting position | on horizontal DIN rail NS 35 in acc. with EN 60715 |

# FB-PA/SC - Repeater

2316375

<https://www.phoenixcontact.com/us/products/2316375>



## Classifications

### ECLASS

ECLASS-13.0

27242608

### ETIM

ETIM 9.0

EC001604

### UNSPSC

UNSPSC 21.0

32151600

# FB-PA/SC - Repeater



2316375

<https://www.phoenixcontact.com/us/products/2316375>

## Environmental product compliance

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)