

UM-2KS40/16AIO/RS/Z/SO225 - Input/output module




2319058

<https://www.phoenixcontact.com/us/products/2319058>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

16/8-channel analog I/O module with spring-cage connection and redundant voltage supply.
Suitable for Yokogawa SAI 143, SAV 144, SAI 533 cards.



Commercial data

Item number	2319058
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C429
Product key	DK2A8N
GTIN	4046356340663
Weight per piece (including packing)	0.34 kg
Weight per piece (excluding packing)	0.34 kg
Customs tariff number	85369010
Country of origin	DE

Technical data

Product properties

Product type	Interface module
--------------	------------------

Insulation characteristics: Air clearances and creepage distances

Overvoltage category	III
Pollution degree	2

Electrical properties

Nominal voltage U_N	30 V DC
Max. current carrying capacity per branch	100 mA

Air clearances and creepage distances

Rated surge voltage	Basic insulation
---------------------	------------------

Supported controller: YOKOGAWA ProSafe-RS

Suitable I/O card	SAI143
	SAI144
	SAI533

Connection data

Field level

Connection method	Spring-cage connection
Number of positions	32
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	Yokogawa, KS compatible
Number of connections	2
Number of positions	40
Tightening torque	0.5 Nm

Signaling

Status display present	no
------------------------	----

Dimensions

Item dimensions

Width	126 mm
Height	168 mm
Depth	45 mm

Environmental and real-life conditions

UM-2KS40/16AIO/RS/Z/SO225 - Input/output module



2319058

<https://www.phoenixcontact.com/us/products/2319058>

Ambient conditions

Ambient temperature (operation)	-20 °C ... 55 °C
---------------------------------	------------------

Standards and regulations

Air clearances and creepage distances

Standards/regulations	DIN EN 50178
-----------------------	--------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com