

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Analog VARIOFACE output module, with COMBICON screw connection and a 25-pos. D-SUB female connector. The signal path can be interrupted with a disconnect knife.

Commercial data

Item number	2319760
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DK2A82
GTIN	4046356427746
Weight per piece (including packing)	200 g
Weight per piece (excluding packing)	200 g
Country of origin	DE

Technical data

Product properties

Product type	Interface module
--------------	------------------

Insulation characteristics: Air clearances and creepage distances

Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	25 V AC
	50 V DC
Max. current carrying capacity per branch	1 A

Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (Basic insulation)

Connection data

Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	D-SUB socket strip
Number of positions	25

Signaling

Status display	no
Status display present	no

Dimensions

Item dimensions

Width	75 mm
Height	111 mm
Depth	56 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	PVC

UM- D25SUB/F/PTS/MSTB/ 374-AO - Output module



2319760

<https://www.phoenixcontact.com/us/products/2319760>

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

Standards and regulations

Air clearances and creepage distances

Standards/regulations	DIN EN 50178
-----------------------	--------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com