

UM-2KS40/16AIO/RS/SO225 - Input/output module




2319838

<https://www.phoenixcontact.com/us/products/2319838>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

16-channel analog input and 8-channel analog output module with screw connection and redundant connector plug. Suitable for Yokogawa SAI 143, SAV 144, SAI 533 cards.



Commercial data

Item number	2319838
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK2A8N
GTIN	4046356441384
Weight per piece (including packing)	339.6 g
Weight per piece (excluding packing)	339.6 g
Customs tariff number	85369010
Country of origin	DE

UM-2KS40/16AIO/RS/SO225 - Input/output module



2319838

<https://www.phoenixcontact.com/us/products/2319838>

Technical data

Product properties

Product type	Interface module
No. of channels	8
	16

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Operating voltage (DC)	≤ 30 V DC
Current (per branch)	≤ 0.1 A

Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (1.2/50 μs)

Supported controller: YOKOGAWA ProSafe-RS

Suitable I/O card	SAI143
	SAV144
	SAI533

Connection data

Connection 1 (control level)

Connection method	Yokogawa, KS compatible
Number of connections	2
Number of positions	40
Tightening torque	0.5 Nm
Pitch	2.54 mm

Connection 2 (field level)

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of positions	32
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section rigid (2 conductors with same cross section)	0.2 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
	0.25 mm ² ... 2.5 mm ² (Ferrule without plastic sleeve)
	0.25 mm ² ... 2.5 mm ² (Ferrule with plastic sleeve)
	0.2 mm ² ... 1.5 mm ²

UM-2KS40/16AIO/RS/SO225 - Input/output module



2319838

<https://www.phoenixcontact.com/us/products/2319838>

Conductor cross-section flexible (2 conductors with same cross section)	0.25 mm ² ... 0.75 mm ² (Ferrule without plastic sleeve)
	0.5 mm ² ... 1.5 mm ² (TWIN ferrule with plastic sleeve)
Conductor cross-section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm
Pitch	5.08 mm

Signaling

Status display present	no
------------------------	----

Dimensions

Item dimensions

Width	168 mm
Height	125.4 mm
Depth	54.6 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection (Module)	IP00
Degree of protection (Installation location)	≤ IP54
Ambient temperature (operation)	-20 °C ... 55 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

Approvals

UKCA

Certificate	UKCA-compliant
-------------	----------------

Standards and regulations

Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

UM-2KS40/16AIO/RS/SO225 - Input/output module




2319838

<https://www.phoenixcontact.com/us/products/2319838>

Drawings

Circuit diagram



UM-2KS40/16AIO/RS/SO225 - Input/output module



2319838

<https://www.phoenixcontact.com/us/products/2319838>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2319838>



EAC

Approval ID: RU*-DE.*08.B.01829*



CSA

Approval ID: LR 13631

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	24 V	0.1 A	-	-

UM-2KS40/16AIO/RS/SO225 - Input/output module



2319838

<https://www.phoenixcontact.com/us/products/2319838>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 10.0	EC002780
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UM-2KS40/16AIO/RS/SO225 - Input/output module



2319838

<https://www.phoenixcontact.com/us/products/2319838>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com