

# AXL F IF CAN 1H - Communication module



2702668

<https://www.phoenixcontact.com/us/products/2702668>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Axioline F, interface module, CAN, transparent protocol, max. transmission speed of 1 Mbps, IP20 protection, including bus base module and Axioline F connectors



## Product description

The module is designed for use within an Axioline F station. This module can be used to integrate a lower-level CAN bus system into the Axioline F station and therefore the bus system used. This Axioline F module acts as the interface for the transparent reading and writing of CAN messages. With appropriate programming on the higher-level controller, it is suitable for CANopen®, J1939, NMEA 2000, and proprietary CAN protocols.

## Your advantages

- Transparent reading and writing of CAN messages
- Integrated buffer memory for 256 CAN messages in the receive direction and 64 CAN messages in the transmit direction
- Parameterizable filter function for 60 filters (11-bit CAN identifier) and 30 filters (29-bit CAN identifier)
- Device rating plate stored
- Diagnostic and status indicators

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2702668       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DR02          |
| Product key                          | DRI253        |
| GTIN                                 | 4055626317175 |
| Weight per piece (including packing) | 189.3 g       |
| Weight per piece (excluding packing) | 189.3 g       |
| Customs tariff number                | 85176200      |
| Country of origin                    | DE            |

# AXL F IF CAN 1H - Communication module




2702668

<https://www.phoenixcontact.com/us/products/2702668>

## Technical data

### Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Width               | 35 mm  |
| Height              | 126.1 mm   |
| Depth               | 54 mm  |
| Note on dimensions  | The depth applies when a TH 35-7.5 DIN rail is used (in accordance with EN 60715). |

### Notes

|                     |                         |
|---------------------|-------------------------|
| Note on application |                         |
| Note on application | Only for industrial use |

### Interfaces

|                     |   |
|---------------------|---|
| Supported protocols | CANopen®  |
|                     | J1939   |
|                     | NMEA 2000   |
|                     | proprietary CAN protocols (with appropriate programming on the higher-level controller) |

#### Axioline F local bus

|                      |                 |
|----------------------|-----------------|
| Number of interfaces | 2               |
| Connection method    | Bus base module |
| Transmission speed   | 100 Mbps        |

#### CAN bus

|                          |  |
|--------------------------|--|
| Number of interfaces     | 1  |
| Connection method        | Push-in connection   |
| Transmission speed range | 10 kbps ... 1 Mbps (Default: 20 kbps)                      |
| Transmission physics     | CAN bus according to standard ISO 11898-2 (high-speed CAN) |

## System properties

### Module

|                         |         |
|-------------------------|---------|
| Process data channel    | 64 Byte |
| Input address area      | 64 Byte |
| Output address area     | 64 Byte |
| Required parameter data | 1 Byte  |

# AXL F IF CAN 1H - Communication module



2702668

<https://www.phoenixcontact.com/us/products/2702668>

|                             |        |
|-----------------------------|--------|
| Required configuration data | 7 Byte |
|-----------------------------|--------|

## Product properties

|                   |   |
|-------------------|---|
| Product type      | I/O component                                       |
| Product family    | Axioline F  |
| Type              | block modular                                       |
| Mounting position | any (no temperature derating)                       |
| Scope of supply   | including bus base module and Axioline F connectors |

## Insulation characteristics

|                      |                              |
|----------------------|------------------------------|
| Overvoltage category | II (IEC 60664-1, EN 60664-1) |
| Pollution degree     | 2 (IEC 60664-1, EN 60664-1)  |

## Electrical properties

|   |        |
|---|--------|
| Maximum power dissipation for nominal condition | 1.35 W |
|---|--------|

### Potentials: Axioline F local bus supply ( $U_{BUS}$ )

|                |                              |
|----------------|------------------------------|
| Supply voltage | 5 V DC (via bus base module) |
| Current draw   | max. 150 mA                  |

### Potentials: Feed-in of supply voltage ( $U_i$ )

|                      |  |
|----------------------|--|
| Supply voltage       | 24 V DC  |
| Supply voltage range | 19.2 V DC ... 30 V DC including all tolerances, including ripple |
| Current draw         | max. 25 mA   |

## Electrical isolation/isolation of the voltage ranges

|  |                        |
|--|------------------------|
| Test voltage: 5 V supply of the local bus ( $U_{BUS}$ ) / 24 V supply (I/Os) | 500 V AC, 50 Hz, 1 min |
| Test voltage: 5 V supply of the local bus ( $U_{BUS}$ ) / CAN I/Os           | 500 V AC, 50 Hz, 1 min |
| Test voltage: 24 V supply (I/O) / CAN I/O                                    | 500 V AC, 50 Hz, 1 min |
| Test voltage: 5 V supply of the local bus ( $U_{BUS}$ ) / functional ground  | 500 V AC, 50 Hz, 1 min |
| Test voltage: 24 V supply (I/O) / functional ground                          | 500 V AC, 50 Hz, 1 min |

## Connection data

### Connection technology

|                               |   |
|-------------------------------|---|
| Connection name               | Axioline F connector  |
| Note on the connection method | Please observe the information provided on conductor cross-sections in the "Axioline F: system and installation" user manual. |

### Axioline F connector

|                                   |   |
|-----------------------------------|---|
| Connection method                 | Push-in connection  |
| Note on the connection method     | Please observe the information provided on conductor cross-sections in the "Axioline F: system and installation" user manual. |
| Conductor cross-section, rigid    | 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>   |
| Conductor cross-section, flexible | 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>   |
| Conductor cross-section AWG       | 24 ... 16   |

# AXL F IF CAN 1H - Communication module



2702668

<https://www.phoenixcontact.com/us/products/2702668>

|                  |      |
|------------------|------|
| Stripping length | 8 mm |
|------------------|------|

## Environmental and real-life conditions

### Ambient conditions

|  |   |
|--|---|
| Ambient temperature (operation)          | -25 °C ... 60 °C                                  |
| Degree of protection                     | IP20  |
| Air pressure (operation)                 | 70 kPa ... 106 kPa (up to 3000 m above sea level) |
| Air pressure (storage/transport)         | 70 kPa ... 106 kPa (up to 3000 m above sea level) |
| Ambient temperature (storage/transport)  | -40 °C ... 85 °C                                  |
| Permissible humidity (operation)         | 5 % ... 95 % (non-condensing)                     |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing)                     |

## Standards and regulations

|                  |                                       |
|------------------|---------------------------------------|
| Protection class | III (IEC 61140, EN 61140, VDE 0140-1) |
|------------------|---------------------------------------|

## Mounting

|                   |                               |
|-------------------|-------------------------------|
| Mounting type     | DIN rail mounting             |
| Mounting position | any (no temperature derating) |

# AXL F IF CAN 1H - Communication module


2702668

<https://www.phoenixcontact.com/us/products/2702668>




## Drawings

Dimensional drawing




## Dimensions

Schematic diagram



Connection example

Block diagram




Internal wiring of the terminal points

2702668

<https://www.phoenixcontact.com/us/products/2702668>

## Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2702668>



**DNV GL**

Approval ID: TAA00000DF



**PRS**

Approval ID: TE/1020/880590/21

**BSH**

Approval ID: 840



**RINA**

Approval ID: ELE008423XG001



**cULus Listed**

Approval ID: E238705

# AXL F IF CAN 1H - Communication module



2702668

<https://www.phoenixcontact.com/us/products/2702668>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27242605 |
| ECLASS-15.0 | 27242605 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001601 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 32151600 |
|-------------|----------|

2702668

<https://www.phoenixcontact.com/us/products/2702668>

## Environmental product compliance

### EU RoHS

|   |              |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |   |
|-------------------------------------|---|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)  |
|                                     | 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1) |
| SCIP                                | baf27848-8d7d-4727-ba5e-2b5d31b12424                        |

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
 586 Fulling Mill Road  
 Middletown, PA 17057, United States  
 (+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)