

GW MODBUS TCP/ASCII 1E/1DB9 - Interface converters



2702768

<https://www.phoenixcontact.com/us/products/2702768>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The GW MODBUS TCP/ASCII... converts RAW or ASCII serial strings into Modbus registers. Includes one RJ45 port and one D-SUB 9 port.



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2702768 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN09 |
| Product key | DNC323 |
| GTIN | 4055626339368 |
| Weight per piece (including packing) | 167 g |
| Weight per piece (excluding packing) | 111 g |
| Customs tariff number | 85176200 |
| Country of origin | US |

GW MODBUS TCP/ASCII 1E/1DB9 - Interface converters



2702768

<https://www.phoenixcontact.com/us/products/2702768>

Technical data

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Utilization restriction

| | |
|----------|---|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---|

Utilization restriction

| | |
|------------|---|
| CCCex note | Use in potentially explosive areas is not permitted in China. |
|------------|---|

Product properties

| | |
|--------------|---|
| Product type | Interface converter |
| MTBF | 92.1 Years (Telcordia standard, 25°C temperature, 50% stress, Environmental Factor = 1.0) |
| | 61.4 Years (Telcordia standard, 40°C temperature, 50% stress, Environmental Factor = 1.5) |

Electrical properties

| | |
|---|---------------------------------------|
| Electrical isolation | IEC UL 61010-1 (VCC // Ethernet) |
| Maximum power dissipation for nominal condition | 1.44 W (at 24 V DC) |
| Test voltage data interface/data interface | 1.5 kV _{rms} (50 Hz, 1 min.) |
| Test voltage data interface/power supply | 1.5 kV _{rms} (50 Hz, 1 min.) |
| | 1.5 kV _{rms} |

Supply

| | |
|-----------------------------|---|
| Supply voltage range | 10.8 V DC ... 30 V DC (via pluggable COMBICON screw terminal block) |
| Typical current consumption | 48 mA (24 V DC) |
| Max. current consumption | 60 mA (24 V DC) |

Function

| | |
|----------------------------------|---|
| Management | Web-based management |
| Status and diagnostic indicators | LEDs: Status, ACT/LNK (Ethernet data traffic) |

Connection data

Supply

| | |
|-----------------------------------|---|
| Conductor cross-section, flexible | 0.20 mm ² ... 2.50 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Tightening torque | 0.5 Nm ... 0.6 Nm |

Interfaces

| | |
|--------|----------|
| Signal | Ethernet |
| | Modbus |

GW MODBUS TCP/ASCII 1E/1DB9 - Interface converters



2702768

<https://www.phoenixcontact.com/us/products/2702768>

| | |
|------------|-----|
| Web server | yes |
|------------|-----|

Data: Modbus/TCP

| | |
|---------------------------|---------------------------------|
| Serial transmission speed | 10/100 Mbps, auto negotiation |
| Connection method | RJ45 jack, shielded |
| No. of channels | 1 |
| Transmission length | ≤ 100 m (shielded twisted pair) |
| Auxiliary protocols | ARP, DHCP (Client), PING |

Data: RS-232

| | |
|-----------------------------|---|
| Serial transmission speed | 0.3; 0.6; 1.2; 2.4; 4.8; 9.6; 19.2; 38.4; 57.6; 115.2; 230.4 Kbps |
| Number of connections | 1 |
| Connection method | D-SUB 9 plug |
| Pin assignment | DTE |
| Transmission length | 15 m |
| File format/coding | 5/6/7/8 Data bits, 1/2 Stop bits, None/Even/Odd/Mark/Space Parity |
| Data flow control/protocols | Software handshake, Xon/Xoff or hardware handshake RTS/CTS |

Data: RS-422

| | |
|---------------------------|---|
| Serial transmission speed | 0.3; 0.6; 1.2; 2.4; 4.8; 9.6; 19.2; 38.4; 57.6; 115.2; 230.4 Kbps |
| Number of connections | 1 |
| Connection method | D-SUB 9 plug |
| Pin assignment | 2, 3, 5, 7, 8 |
| Transmission length | ≤ 1200 m |
| Termination resistor | 120 Ω (configurable) |
| File format/coding | 5/6/7/8 Data bits, 1/2 Stop bits, None/Even/Odd/Mark/Space Parity |

Data: RS-485

| | |
|---------------------------|---|
| Serial transmission speed | 0.3; 0.6; 1.2; 2.4; 4.8; 9.6; 19.2; 38.4; 57.6; 115.2; 230.4 Kbps |
| Number of connections | 1 |
| Connection method | D-SUB 9 plug |
| Pin assignment | 3, 5, 7 |
| Termination resistor | 120 Ω (configurable) |
| File format/coding | 5/6/7/8 Data bits, 1/2 Stop bits, None/Even/Odd/Mark/Space Parity |

Dimensions

| | |
|--------|---------|
| Width | 22.5 mm |
| Height | 99 mm |
| Depth | 115 mm |

Material specifications

| | |
|------------------|-----------------------|
| Color (Housing) | light gray (RAL 7035) |
| Housing material | PA 6.6 |

GW MODBUS TCP/ASCII 1E/1DB9 - Interface converters



2702768

<https://www.phoenixcontact.com/us/products/2702768>

Mechanical tests

| | |
|--|---|
| Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6 | : |
| Shock in accordance with EN 60068-2-27/IEC 60068-2-27 | : |

Environmental and real-life conditions

Ambient conditions

| | |
|--|--------------------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 70 °C |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Altitude | < 2000 m |
| Permissible humidity (operation) | 10 % ... 95 % (non-condensing) |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing) |

Approvals

Conformity/Approvals

| | |
|------------------|--|
| Conformance | CE-compliant |
| UL, USA | UL 61010-1 |
| UL, USA / Canada | Class I, Div. 2, Groups A, B, C, D T4A |
| Noxious gas test | ISA-S71.04-1985 G3 Harsh Group A |

Ex data

| | |
|-------|---|
| ATEX | DEMKO 18ATEX 2026X: II 3 G Ex ec IIC T4 Gc |
| IECEX | IECEX UL 18.0023X Ex ec IIC T4 Gc |

EMC data

| | |
|-------------------------------|---|
| Electromagnetic compatibility | Conformance with EMC Directive 2014/30/EU |
| Noise immunity | EN 61000-6-2:2005 |

Noise emission

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

Standards and regulations

| | |
|-----------------------|--------------------|
| Standards/regulations | EN 55022, EN 55024 |
|-----------------------|--------------------|

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

GW MODBUS TCP/ASCII 1E/1DB9 - Interface converters



2702768

<https://www.phoenixcontact.com/us/products/2702768>

Drawings

Block diagram



GW MODBUS TCP/ASCII 1E/1DB9 - Interface converters



2702768

<https://www.phoenixcontact.com/us/products/2702768>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2702768>


 **UL Listed**
Approval ID: E238705

 **cUL Listed**
Approval ID: E238705

 **IECEX**
Approval ID: IECEX UL 18.0023X

 **cUL Listed**
Approval ID: E196811

 **UL Listed**
Approval ID: E196811

 **ATEX**
Approval ID: DEMKO 18 ATEX 2026X

GW MODBUS TCP/ASCII 1E/1DB9 - Interface converters



2702768

<https://www.phoenixcontact.com/us/products/2702768>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27242208 |
| ECLASS-15.0 | 27242208 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43222600 |
|-------------|----------|

GW MODBUS TCP/ASCII 1E/1DB9 - Interface converters



2702768

<https://www.phoenixcontact.com/us/products/2702768>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com