

# FLKM-2KS50/AAR145/Z/YCS - Passive module



2321871

<https://www.phoenixcontact.com/us/products/2321871>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE interface module with spring-cage connection, for Yokogawa RTD module AAR145.

## Commercial data

Item number	2321871
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK218N
GTIN	4046356422475
Weight per piece (including packing)	275 g
Weight per piece (excluding packing)	275 g
Customs tariff number	85369010
Country of origin	DE

# FLKM-2KS50/AAR145/Z/YCS - Passive module



2321871

<https://www.phoenixcontact.com/us/products/2321871>

## Technical data

### Product properties

Product type	Interface module
No. of channels	16
Operating mode	100% operating factor

### Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

### Electrical properties

Operating voltage (DC)	≤ 30 V DC
Current (per branch)	≤ 0.1 A

### Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (1.2/50 μs)

### Supported controller: YOKOGAWA CS3000 CentumVP

Suitable I/O card	AAR145
-------------------	--------

## Connection data

### Connection 1 (control level)

Connection method	Yokogawa, KS compatible
Number of connections	2
Number of positions	50
Note	Usable system cables: Phoenix Contact YUC50, Yokogawa AKB331
Tightening torque	0.5 Nm
Pitch	2.54 mm

### Connection 2 (field level)

Connection method	Spring-cage connection
Stripping length	7.5 mm
Number of positions	48
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
	0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (Ferrule without plastic sleeve)
	0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (Ferrule with plastic sleeve)
Conductor cross-section AWG	24 ... 14
Pitch	5.08 mm

## Signaling

# FLKM-2KS50/AAR145/Z/YCS - Passive module



2321871

<https://www.phoenixcontact.com/us/products/2321871>

Status display present	no
------------------------	----

## Dimensions

### Item dimensions

Width	168.65 mm
Height	77 mm
Depth	51.3 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (Module)	IP20
Degree of protection (Installation location)	≤ IP54
Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

## Approvals

### UKCA

Certificate	UKCA-compliant
-------------	----------------

## Standards and regulations

### Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# FLKM-2KS50/AAR145/Z/YCS - Passive module




2321871

<https://www.phoenixcontact.com/us/products/2321871>

## Drawings

Dimensional drawing




# FLKM-2KS50/AAR145/Z/YCS - Passive module



2321871

<https://www.phoenixcontact.com/us/products/2321871>

## Circuit diagram



# FLKM-2KS50/AAR145/Z/YCS - Passive module



2321871

<https://www.phoenixcontact.com/us/products/2321871>

## Classifications

### ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

### ETIM

ETIM 10.0	EC002780
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# FLKM-2KS50/AAR145/Z/YCS - Passive module



2321871

<https://www.phoenixcontact.com/us/products/2321871>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)