

# FLKM-2KS50/PMT/ADV151/Z/YCS - Passive module



2321923

<https://www.phoenixcontact.com/us/products/2321923>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE input module with spring-cage connection, 32 channels, redundant connector for Yokogawa input modules ADV151, ADV161.

## Commercial data

Item number	2321923
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK218N
GTIN	4046356418478
Weight per piece (including packing)	670.1 g
Weight per piece (excluding packing)	643 g
Customs tariff number	85389091
Country of origin	DE

## Technical data

### Product properties

Product type	Interface module
No. of channels	32
Operating mode	100% operating factor

Insulation characteristics: Air clearances and creepage distances between the power circuits

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

### Electrical properties

Operating voltage (DC)	24 V DC
Operating voltage range	19.2 V DC ... 30 V DC
Current (Per path)	≤ 63 mA (protected by slow-blow fuse 63 mA, observe derating)
Current (Total current)	≤ 2 A (protected by fuse (2 AT), observe derating)

Air clearances and creepage distances between the power circuits

Rated insulation voltage	50 V DC
Rated surge voltage	0.5 kV

Supported controller: YOKOGAWA CS3000 CentumVP

Suitable I/O card	ADV151
	ADV161

Supported controller: YOKOGAWA STARDOM

Suitable I/O card	NFDV151
	NFDV161

### Output data

K1

Contact switching type	Double contact, 1 N/O contact
Contact material	AgNi 90/10, + 5 µm hard gold-plated
Maximum switching voltage	48 V DC
	≤ 25 V AC
Limiting continuous current	1 A
Min. switching current	1 mA
Interrupting rating (ohmic load) max.	24 W (24 V DC)
	48 W (48 V DC)
	25 VA (25 V AC)
Mechanical service life	approx. 2x 10 <sup>7</sup> cycles

### Connection data

# FLKM-2KS50/PMT/ADV151/Z/YCS - Passive module



2321923

<https://www.phoenixcontact.com/us/products/2321923>

## Field level

Connection method	Spring-cage connection
Number of connections	1
Number of positions	64
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

## Controller level

Connection method	Yokogawa, KS compatible
Number of connections	2
Number of positions	50
Note	Usable system cables: Phoenix Contact YUC50, Yokogawa AKB331
Tightening torque	0.5 Nm

## Signaling

Status display present	yes
Operating voltage display	Green LED

## Dimensions

### Item dimensions

Width	231.6 mm
Height	111.8 mm
Depth	65.5 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

## Standards and regulations

### Air clearances and creepage distances between the power circuits

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

## Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

## Notes

# FLKM-2KS50/PMT/ADV151/Z/YCS - Passive module



2321923

<https://www.phoenixcontact.com/us/products/2321923>

Notes on operation	No additional touch protection is required when using a SELV/PELV voltage ( $\leq 25$ V AC or 60 V DC).
Notes on operation	At least one functional insulation against adjacent modules is complied with (in the support rail direction). If the application has stricter requirements for the insulation (basic insulation or reinforced insulation), they must be realized by applying suitable measures (e. g. partition plates).
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

# FLKM-2KS50/PMT/ADV151/Z/YCS - Passive module




2321923

<https://www.phoenixcontact.com/us/products/2321923>

## Drawings

Dimensional drawing




# FLKM-2KS50/PMT/ADV151/Z/YCS - Passive module



2321923


<https://www.phoenixcontact.com/us/products/2321923>

Dimensional drawing



Labeling 33B..64B/33A..64A and the additional sticker 64DI X is included with the packing.

## Circuit diagram



2321923

<https://www.phoenixcontact.com/us/products/2321923>

## Classifications

### ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

### ETIM

ETIM 10.0	EC002780
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

2321923

<https://www.phoenixcontact.com/us/products/2321923>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	6d22207b-4aa3-43a5-ae38-fbf3d4f2ad45

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
 586 Fulling Mill Road  
 Middletown, PA 17057, United States  
 (+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)