

# VIP-2/SC/FLK10/LED - Termination board



2322045

<https://www.phoenixcontact.com/us/products/2322045>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with screw connection and flat-ribbon cable connector, for mounting on NS 35 rails, with pin strip and short and long locking latches for socket strips, 10-pos., with LED

## Your advantages

- 10-pos. ... 64-pos.
- Metal foot
- In accordance with IEC 60603-13
- 1:1 connection
- Screw connection

## Commercial data

Item number	2322045
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C423
Product key	DK2111
GTIN	4046356450829
Weight per piece (including packing)	92.4 g
Weight per piece (excluding packing)	91.6 g
Customs tariff number	85366990
Country of origin	US

# VIP-2/SC/FLK10/LED - Termination board



2322045

<https://www.phoenixcontact.com/us/products/2322045>

## Technical data

### Product properties

Product type	Interface module
Product family	VARIOFACE Professional
Number of positions	10

### Insulation characteristics

Overvoltage category	II
Pollution degree	2

### Electrical properties

Nominal voltage $U_N$	24 V DC
Max. current carrying capacity per branch	1 A

### Connection data

#### Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

#### Controller level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	10
Pitch	2.54 mm

### Signaling

Status display	LED
Status display present	yes

### Dimensions

#### Item dimensions

Width	34.7 mm
Height	65.5 mm
Depth	56 mm

### Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0

# VIP-2/SC/FLK10/LED - Termination board



2322045

<https://www.phoenixcontact.com/us/products/2322045>

Housing insulation material	Polyamide PA non-reinforced
-----------------------------	-----------------------------

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

## Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# VIP-2/SC/FLK10/LED - Termination board




2322045

<https://www.phoenixcontact.com/us/products/2322045>

## Drawings

Circuit diagram



# VIP-2/SC/FLK10/LED - Termination board



2322045

<https://www.phoenixcontact.com/us/products/2322045>

## Classifications

### UNSPSC

UNSPSC 21.0	39121432
-------------	----------

# VIP-2/SC/FLK10/LED - Termination board



2322045

<https://www.phoenixcontact.com/us/products/2322045>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)