

VIP-2/SC/FLK14/8M/PLC - Passive module



2322281

<https://www.phoenixcontact.com/us/products/2322281>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE interface module, for 8 channels, each with an additional terminal block per signal for a common minus potential

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2322281 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C423 |
| Product key | DK2111 |
| GTIN | 4046356451178 |
| Weight per piece (including packing) | 116.1 g |
| Weight per piece (excluding packing) | 116 g |
| Customs tariff number | 85366990 |
| Country of origin | US |

VIP-2/SC/FLK14/8M/PLC - Passive module



2322281

<https://www.phoenixcontact.com/us/products/2322281>

Technical data

Product properties

| | |
|---------------------|------------------------|
| Product type | Interface module |
| Product family | VARIOFACE Professional |
| Number of positions | 14 |
| No. of channels | 8 |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree | 2 |

Electrical properties

| | |
|------------------------|------------------|
| Operating voltage (AC) | ≤ 25 V AC |
| Operating voltage (DC) | ≤ 60 V DC |
| Current (per branch) | ≤ 1 A |
| Current () | ≤ 3 A (per byte) |
| Rated surge voltage | 0.6 kV |

Supported controller: SIEMENS S7-1500

| | |
|-------------------|---|
| Suitable I/O card | 6ES7521-1BH00-0AB0 |
| | 6ES7521-1BH10-0AA0 |
| | 6ES7521-1BH50-0AA0 |
| | 6ES7521-1BL00-0AB0 |
| | 6ES7521-1BL10-0AA0 |
| | 6ES7521-1BP00-0AA0 (Sinking mode) |
| | 6ES7522-1BH00-0AB0 |
| | 6ES7522-1BH01-0AB0 |
| | 6ES7522-1BL00-0AB0 |
| | 6ES7522-1BL01-0AB0 |
| | 6ES7522-1BL10-0AA0 |
| | 6ES7522-1BP00-0AA0 |
| | 6ES7522-1BP50-0AA0 |
| | 6ES7523-1BL00-0AA0 |
| | 6ES7523-1BP50-0AA0 (DI32 (Sinking mode)/DQ32) |

Supported controller: ABB S800 I/O

| | |
|-------------------|-------|
| Suitable I/O card | DI814 |
| | DO810 |
| | DO840 |

Supported controller: ALLEN-BRADLEY ControlLogix

| | |
|-------------------|-----------|
| Suitable I/O card | 1756-IB32 |
| | 1756-OB32 |
| | 1756-IN16 |

VIP-2/SC/FLK14/8M/PLC - Passive module



2322281

<https://www.phoenixcontact.com/us/products/2322281>

| | |
|--|------------|
| | 1756-IB16 |
| | 1756-IC16 |
| | 1756-OB16E |

Supported controller: GE-FANUC RX3i

| | |
|-------------------|-------------|
| Suitable I/O card | IC694MDL754 |
| | IC694MDL660 |

Supported controller: HONEYWELL Experion PKS C200

| | |
|-------------------|------------|
| Suitable I/O card | TC-IDD 321 |
| | TC-ODD 321 |

Supported controller: MITSUBISHI MELSEC L

| | |
|-------------------|----------|
| Suitable I/O card | LX41C4 |
| | LX42C4 |
| | LY41NT1P |
| | LY42NT1P |
| | LY41PT1P |
| | LY42PT1P |

Supported controller: MITSUBISHI MELSEC Q

| | |
|-------------------|---------|
| Suitable I/O card | QX81 |
| | QY81P |
| | QX41 |
| | QX41-S1 |
| | QX42 |
| | QX42-S1 |
| | QX71 |
| | QX72 |
| | QY41P |
| | QY42P |
| | QY71 |
| | QH42P |
| | QX82 |
| | QX82-S1 |
| | QY82P |

Supported controller: SIEMENS S7-300 / ET 200 M

| | |
|-------------------|--------------------|
| Suitable I/O card | CPU 313C-2DP |
| | CPU 314C-2DP |
| | CPU 314C-2PiP |
| | 6ES7321-1BH02-0AA0 |
| | 6ES7321-1BL00-0AA0 |
| | 6ES7322-1BH01-0AA0 |
| | 6ES7322-1BL00-0AA0 |
| | 6ES7323-1BH01-0AA0 |

VIP-2/SC/FLK14/8M/PLC - Passive module



2322281

<https://www.phoenixcontact.com/us/products/2322281>

| | |
|--|--------------------|
| | 6ES7323-1BL00-0AA0 |
| Supported controller: SCHNEIDER ELECTRIC Modicon TSX QUANTUM | |
| Suitable I/O card | DDI 353 |
| | DDI 853 |
| | DAI 453 |
| | DDO 353 |

Connection data

Field level

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Number of positions | 14 |
| Conductor cross-section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Tightening torque | 0.5 Nm ... 0.6 Nm |

Controller level

| | |
|-----------------------|-------------------|
| Connection method | IDC/FLK pin strip |
| Number of connections | 1 |
| Number of positions | 14 |
| Pitch | 2.54 mm |

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Dimensions

Item dimensions

| | |
|--------|---------|
| Width | 50 mm |
| Height | 65.5 mm |
| Depth | 56 mm |

Material specifications

| | |
|--|-----------------------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 | V0 |
| Housing insulation material | Polyamide PA non-reinforced |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

VIP-2/SC/FLK14/8M/PLC - Passive module



2322281

<https://www.phoenixcontact.com/us/products/2322281>

Standards and regulations

| | |
|-----------------------|--------------|
| Standards/regulations | IEC 60664 |
| | DIN EN 50178 |

Mounting

| | |
|-------------------|-------------------|
| Mounting type | DIN rail mounting |
| Mounting position | any |

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

VIP-2/SC/FLK14/8M/PLC - Passive module




2322281

<https://www.phoenixcontact.com/us/products/2322281>

Drawings

Circuit diagram



Connection scheme VIP-2/.../FLK14/8M/PLC

VIP-2/SC/FLK14/8M/PLC - Passive module





2322281

<https://www.phoenixcontact.com/us/products/2322281>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2322281>

|  cUL Recognized Approval ID: E238705 | | | | |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 125 V | 1 A | 30 - 12 | - |

|  UL Recognized Approval ID: E238705 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 125 V | 1 A | 30 - 12 | - |

VIP-2/SC/FLK14/8M/PLC - Passive module



2322281

<https://www.phoenixcontact.com/us/products/2322281>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27141152 |
| ECLASS-15.0 | 27141152 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002780 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

VIP-2/SC/FLK14/8M/PLC - Passive module



2322281

<https://www.phoenixcontact.com/us/products/2322281>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com