# FL NAT 2208 - Industrial Ethernet Switch

2702882

https://www.phoenixcontact.com/us/products/2702882

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

CRA-READY



Managed NAT Switch 2000 series, 8 RJ45 ports 10/100 Mbps, degree of protection: IP20, Ambient temperature (operation): -40 °C ... 70 °C, Supply voltage range: 9 V DC ... 57 V DC, PROFINET Conformance Class B, 1:1-NAT, Virtual NAT, IP-Masquerading, Development process certified in accordance with IEC 62443-4-1, Product certified in accordance with IEC 62443-4-2, The product is being prepared for compliance with the Cyber Resilience Act (CRA)

## Your advantages

- 1:1 NAT, virtual NAT, IP masquerading, port forwarding
- Flexible distribution into several LAN and WAN areas
- Ambient temperature -40 °C ... 70 °C
- MRP (client and manager)
- VLANs
- RSTP
- DHCP client, DHCP server (pool-based and port-based), DHCP option 82
- Slim design
- Web-based management, SNMP
- Configuration memory
- Easy and fast startup and commissioning with the FL NETWORK MANAGER software
- Suitable for PROFINET and EtherNet/IP™ networks


ELEKTROGERÄTE RÜCKNAHME

## Commercial data

| | |
|---|---|
| Item number | 2702882 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN17 |
| Product key | DNN131 |
| GTIN | 4055626384825 |
| Weight per piece (including packing) | 329 g |
| Weight per piece (excluding packing) | 230 g |
| Customs tariff number | 85176200 |
| Country of origin | DE |

## Technical data

### Dimensions

| | |
|---|---|
| Dimensional drawing |   |
| Width | 45 mm |
| Height | 130 mm |
| Depth | 115 mm |

### Notes

| | |
|---|---|
| Note on application | Support by phone or on-site (fee is charged) |
| Note on application | Only for industrial use |
| Note on application | As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA. |

### Material specifications

| | |
|---|---|
| Color (Housing) | gray (RAL 7042) |
| Color (Cover) | light gray (RAL 7035) |
| Housing material | Polycarbonate fiber reinforced |

### Mounting

| | |
|---|---|
| Mounting type | DIN rail mounting |

### Interfaces

Ethernet (RJ45)

| | |
|---|---|
| Connection method | RJ45 |
| Note on the connection method | Auto negotiation and autocrossing |
| Transmission speed | 10/100 Mbps |
| Transmission physics | Copper |
| Transmission length | 100 m (per segment) |
| Signal LEDs | Data receive, link status |
| No. of channels | 8 (RJ45 ports) |

### Output data

Digital:

| | |
|---|---|
| Output name | Alarm output |

Signal contact

| | |
|---|---|
| Output name | Digital output |
| Control voltage | typ. 24 V DC |
| Actuation voltage range | 9 V DC ... 57 V DC |
| Current carrying capacity | typ. 100 mA |
| | max. 0.7 A (1 minute) |

## Product properties

| | |
|---|---|
| Product type | Switch |
| Product family | Managed NAT Switch 2000 |
| Type | Book type |
| MTTF | 494.02 Years (SN 29500 standard, temperature 25°C, operating cycle 21%) |
| | 235.18 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%) |
| | 29.73 Years (SN 29500 standard, temperature 70°C, operating cycle 100%) |
| Special properties | 1:1-NAT, Virtual NAT, IP-Masquerading |
| | Development process certified in accordance with IEC 62443-4-1 |
| | Product certified in accordance with IEC 62443-4-2 |
| | The product is being prepared for compliance with the Cyber Resilience Act (CRA) |
| Signal delay | ≥ 6.5 µs (Store and Forward mode, 10/100 Mbps, depending on the frame size) |

### Insulation characteristics

| | |
|---|---|
| Protection class | III (VDE 0106) |
| Degree of pollution | 2 |

### Switch functions

| | |
|---|---|
| IP parameterization | DHCP client |
| | DHCP Option 82 (Relay Agent) |
| | DHCP server (pool-based, port-based) |
| | BootP |
| | DCP (Discovery and Configuration Protocol) |
| MAC address table | 8k |
| Signal contact control voltage | typ. 24 V DC |
| PROFINET conformance class | Conformance Class B |
| PROFINET device function | PROFINET device |
| Status and diagnostic indicators | LEDs: US1, US2 (power supply), Fail (alarm contact), 2 LEDs per Ethernet port (Link/Activity and Speed) |
| Basic functions | Store-and-forward switch, complies with IEEE 802.3 |
| Management functions | Web-based management (HTTP/HTTPS) |
| | Role-based user management (LDAP, RADIUS) |
| | SNMPv1/v2/v3 |
| | Command Line Interface (Telnet, SSH) |
| Diagnostic functions | RMON History |
| | LLDP (Link Layer Discovery Protocol) |

| | |
|---|---|
| | SNMP-Traps |
| | N:1-Portmirroring |
| | ACD (Address Conflict Detection) |
| | SysLog |
| | CRC-Surveillance |
| Filter functions | Quality of Service (8 priority classes) |
| | Class of Service |
| | DiffServ/DSCP |
| | Port-Priorisierung |
| | VLAN (up to 32 VLANs) |
| | IGMP Snooping/Querier (v1/v2) |
| | Auto-Query-Port |
| | Extended Multicast Filtering |
| NAT functions | 1:1-NAT |
| | Virtual-NAT |
| | IP-Masquerading |
| | Port forwarding |
| Redundancy functions | MRP (Media Redundancy Protocol) |
| | RSTP (Rapid Spanning Tree Protocol) |
| | FRD (Fast Ring Detection) |
| | Large Tree Support |
| | LACP (Link Aggregation Control Protocol) |
| | PROFINET S2 system redundancy |
| Time synchronization | SNTP (Simple Network Time Protocol) |

Security functions

| | |
|---|---|
| Port security | MAC-based, RADIUS (IEEE 802.1X), MAC Authentication Bypass |

## Electrical properties

| | |
|---|---|
| Current consumption | 190 mA |
| Local diagnostics | US1/2 Supply voltage US1, US2 Green LED |
| | FAIL Div. LED red |
| | LINK Link status Green LED |
| Maximum power dissipation for nominal condition | 4.95 W (At $U_S$ = 9 V DC and 70°C ambient temperature) |
| Test section | 24 V supply / functional ground 500 V DC 1 min |
| | Ethernet interface/all other potentials 2.25 kV DC |
| Transmission medium | Copper |

Supply

| | |
|---|---|
| Supply voltage (DC) | 24 V DC (redundant) |
| Supply voltage range | 9 V DC ... 57 V DC |
| Power supply connection | via COMBICON, max. conductor cross-section 1.5 mm² |
| Residual ripple | 3.6 $V_{PP}$ (within the permitted voltage range) |
| Max. current consumption | 1.3 A ($U_S$ = Min, $T_{amb}$ = Max, $DO_I$ = Max) |

| | |
|---|---|
| Typical current consumption | 185 mA (at $U_S$ = 24 V DC and 25 °C ambient temperature) |
| Current consumption | 190 mA |
| Ground connection | Via DIN rail |
| Functional grounding | The functional ground of the module is grounded when it is snapped onto a grounded DIN rail |

## Connection data

| | |
|---|---|
| Connection method | Screw connection |
| Note on the connection method | Use only copper connecting cables providing the permitted temperature range (-40 °C ... 75 °C) |
| pluggable | yes |
| Conductor cross-section, rigid | 0.08 mm² ... 1.5 mm² |
| Conductor cross-section, flexible | 0.08 mm² ... 1.5 mm² |
| Conductor cross-section AWG | 28 ... 16 |
| Stripping length | 7 mm |

## Environmental and real-life conditions

### Ambient conditions

| | |
|---|---|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 70 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Permissible humidity (operation) | 10 % ... 95 % (non-condensing) |
| Permissible humidity (storage/transport) | 10 % ... 95 % (non-condensing) |
| Shock (operation) | 30g (EN 60068-2-27) |
| Vibration (operation) | in acc. with IEC 60068-2-6: 5g, 150 Hz |
| Air pressure (operation) | 80 kPa ... 110 kPa up to 2000 m above mean sea level (Without derating) |
| Air pressure (storage/transport) | 79 kPa ... 108 kPa up to 2000 m above mean sea level (Without derating) |

## Standards and regulations

| | |
|---|---|
| Free from substances that could impair the application of coating | Yes |

## Approvals

### ATEX

| | |
|---|---|
| Identification | Ⓔx II 3 G Ex ec IIC T4 Gc |
| Certificate | DEMKO 16 ATEX 1709X |

### IECEx

| | |
|---|---|
| Identification | Ex ec IIC T4 Gc |
| Certificate | IECEx ULD 16.0018 X |

### UL, USA/Canada

| | |
|---|---|
| Identification | cULus |

### UL Ex, USA / Canada

| | |
|---|---|
| Identification | Class I, Division 2, Groups A, B, C, and D, T4 |
| | Class I, Zone 2, AEx ec IIC T4 |
| | Ex ec IIC T4 Gc X |
| Certificate | E366272 |
| Note | UL 60079-0 Ed. 6 / UL 60079-7 Ed. 5, CSA 22.2 No. 60079-0 Ed. 3 / CSA C22.2 No. 60079-7 Ed. 2 |

EAC Ex

| | |
|---|---|
| Identification | 2Ex e IIC T4 Gc X |
| Certificate | RU C-DE.HB49.B.00118/21 |

The following continue to apply for EAC Ex:

| | |
|---|---|
| Identification | Install the device in a suitable, approved housing with at least IP66 protection. |
| | The housing/control cabinet must be equipped with a warning sign prohibiting opening in the potentially explosive area. |
| | The operation of devices is permitted if all optical ports are connected or sealed with the supplied filler plugs. |

CCC / China-Ex

| | |
|---|---|
| Identification | Ex ec IIC T4 Gc |
| Certificate | 2022122310115629 |

Corrosive gas test

| | |
|---|---|
| Identification | ISA S71.04.2013 G3 Harsh Group A |

UKCA Ex (UKEX)

| | |
|---|---|
| Identification | Ⓔx II 3 G Ex ec IIC T4 Gc |
| Certificate | PxCIMA22UKEX2702910X |

Shipbuilding data

| | |
|---|---|
| Temperature | B |
| Humidity | B |
| Vibration | A |
| EMC | B |
| Enclosure | Required protection according to the Rules shall be provided upon installation on board |

## EMC data

| | |
|---|---|
| Electromagnetic compatibility | Conformance with EMC Directive 2014/30/EU |
| Conformance with EMC directives | EN 61000-6-2 EN 61000-4-2 (ESD) Criterion B |
| | EN 61000-6-2 EN 61000-4-3 (electromagnetic fields) Criterion A |
| | EN 61000-6-2 EN 61000-4-4 (EFT burst) Criterion A |
| | EN 61000-6-2 EN 61000-4-5 (surge) Criterion B |
| | EN 61000-6-2 EN 61000-4-6 (line noise immunity) Criterion A |
| | EN 61000-6-2 EN 61000-6-4 (interference) Class A |
| | EN 61000-6-2 EN 61000-6-4 (conducted interference) Class A |
| Noise immunity | EN 61000-6-2 |

Noise emission


| | |
|---|---|
| Standards/regulations | EN 61000-6-4 |

## Signaling

| | |
|---|---|
| Status display | LEDs: US1, US2 (power supply), Fail (alarm contact), 2 LEDs per Ethernet port (Link/Activity and Speed) |

## Drawings

Dimensional drawing



## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2702882

**DNV GL**
Approval ID: TAA00000YV

**LR**
Approval ID: LR22250919TA

**NK**
Approval ID: TA24215M

**BV**
Approval ID: 48146_B1 BV

**BSH**
Approval ID: Nr. 966

**RINA**
Approval ID: ELE014724XG001

**ABS**
Approval ID: 21_2066186_1_PDA

**cULus Listed**
Approval ID: E238705

**Cybersecurity Certificate**
Approval ID: 968 CSP 1043.00 25

**ABS**
Approval ID: 26-0501235-PDA

**IECEx**
Approval ID: IECEx ULD 16.0018X

**ATEX**
Approval ID: DEMKO 16 ATEX 1709X

**CCC**
Approval ID: 2022122310115629

**cULus Listed**
Approval ID: E366272

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 19170401 |
| ECLASS-15.0 | 19170401 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000734 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 43222600 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | db0dfb23-49f3-4d28-9df1-abe95d18712b |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com