

# AXL F SGI2 1H - Analog module

2702911

<https://www.phoenixcontact.com/us/products/2702911>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Axioline F, Strain gauge capture module, transmission speed in the local bus: 100 Mbps, degree of protection: IP20, including bus base module and Axioline F connectors

## Product description

The module is designed for use within an Axioline F station. Used to evaluate strain gauges that may be located in weighing cells or load cells, for example. You can connect the strain gauges using 6- or 4-conductor technology.

## Your advantages

- 2 high-precision inputs for strain gauges
- Measuring ranges adjusted with nominal characteristic values upon delivery
- Manual entry of characteristic values
- Process data update can be parameterized in increments between 200  $\mu$ s and 100 ms
- Path adjustment in the process environment
- 2-point adjustment
- Connection of strain gauges in 6- and 4-conductor technology
- Advanced wire-break detection
- Sensor supply of up to 115 mA (8 load cells with 350  $\Omega$  per channel)
- Per channel: low-resistance, floating N/O contact
- The channels are parameterized independently of one another via the bus system
- Tara device

## Commercial data

Item number	2702911
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR02
Product key	DRI244
GTIN	4055626459288
Weight per piece (including packing)	181.5 g
Weight per piece (excluding packing)	181.5 g
Customs tariff number	85389091
Country of origin	DE

# AXL F SGI2 1H - Analog module

2702911

<https://www.phoenixcontact.com/us/products/2702911>

## Technical data

### Dimensions

Dimensional drawing	
Width	35 mm
Height	126.1 mm
Depth	54 mm
Note on dimensions	The depth applies when a TH 35-7.5 DIN rail is used (in accordance with EN 60715).

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Material specifications

Color (Housing)	gray (RAL 7042)
-----------------	-----------------

### Interfaces

#### Axioline F local bus

Number of interfaces	2
Connection method	Bus base module
Transmission speed	100 Mbps

### System properties

#### Programming data (LocalbusSlave)

Input address area	12 Byte
Output address area	12 Byte

#### Fieldbus data telegram (PROFIBUS)

Required parameter data	48 Byte
Required configuration data	7 Byte

### Input data

#### Analog

Description of the input	Input channels for strain gauge
Number of inputs	2
Connection technology	6 or 4-wire, twisted pair shielded cable

# AXL F SGI2 1H - Analog module



2702911

<https://www.phoenixcontact.com/us/products/2702911>

Bridge difference $U_d$	Measuring range specified by selecting the characteristic -35 mV ... +35 mV
Bridge voltage $U_0$	5 V
Measured value representation	32 bits
Characteristics	can be parameterized: 350 $\mu$ V/V ... 6500 $\mu$ V/V

## Contacts

Description	Floating N/O contact
Quantity	2 ( $K_{a1}$ - $K_{b1}$ , $K_{a2}$ - $K_{b2}$ )
Contact resistance	< 1 $\Omega$ (typical) < 3 $\Omega$ (maximum)
Typical response time	typ. 0.2 ms (opening) typ. 2 ms (close)

## Output data

### Analog

Output description	Jumper supply
Number of outputs	2
Impedance	> 43 $\Omega$ (per channel)
Output voltage	typ. 5 V
Output current	max. 115 mA (per channel)

## Product properties

Product type	I/O component
Product family	Axioline F
Type	block modular
Mounting position	any (no temperature derating)
Scope of supply	including bus base module and Axioline F connectors
Operating mode	Process data mode with 6 words

### Insulation characteristics

Overvoltage category	II (IEC 60664-1, EN 60664-1)
Pollution degree	2 (IEC 60664-1, EN 60664-1)

## Electrical properties

Maximum power dissipation for nominal condition	1.85 W
---	--------

### Potentials: Axioline F local bus supply ( $U_{Bus}$ )

Supply voltage	5 V DC (via bus base module)
Current draw	max. 75 mA typ. 65 mA

### Potentials: Supply for analog modules ( $U_A$ )

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)

# AXL F SGI2 1H - Analog module



2702911

<https://www.phoenixcontact.com/us/products/2702911>

Current draw	typ. 110 mA (with maximum load: 8 weighing cells with 350 Ω per channel)
	typ. 25 mA (with typical load: 1 weighing cell with 350 Ω, only one channel loaded)
	typ. 55 mA (with maximum load: 8 weighing cells with 350 Ω, only one channel loaded)
Current consumption	typ. 15 mA (with no load, no weighing cell)
Protective circuit	Surge protection; Suppressor diode
	Reverse polarity protection; Polarity protection diode

## Electrical isolation/isolation of the voltage ranges

Test voltage: Logic	500 V AC, 50 Hz, 1 min
Test voltage: 24 V supply (I/O)	500 V AC, 50 Hz, 1 min
Test voltage: Analog inputs	500 V AC, 50 Hz, 1 min
Test voltage: N/O contact K <sub>a1</sub> - K <sub>b1</sub>	500 V AC, 50 Hz, 1 min
Test voltage: N/O contact K <sub>a2</sub> - K <sub>b2</sub>	500 V AC, 50 Hz, 1 min
Test voltage: Functional ground	500 V AC, 50 Hz, 1 min

## Connection data

### Connection technology

Connection name	Axioline F connector
Note on the connection method	Please observe the information provided on conductor cross-sections in the "Axioline F: system and installation" user manual.
	Applications with UL approval: only use copper conductors.

### Axioline F connector

Connection method	Push-in connection
Note on the connection method	Please observe the information provided on conductor cross-sections in the "Axioline F: system and installation" user manual.
	Applications with UL approval: only use copper conductors.
Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 16
Stripping length	8 mm

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)

### Mechanical test

# AXL F SGI2 1H - Analog module



2702911

<https://www.phoenixcontact.com/us/products/2702911>

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	5g
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	30g
Continuous shock in accordance with EN 60068-2-27/IEC 60068-2-27	10g

## Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any (no temperature derating)

# AXL F SGI2 1H - Analog module

2702911


<https://www.phoenixcontact.com/us/products/2702911>

## Drawings

Dimensional drawing



Connection diagram




# AXL F SGI2 1H - Analog module

2702911

<https://www.phoenixcontact.com/us/products/2702911>

Connection diagram




Connection of several strain gauges in 6-conductor technology

# AXL F SGI2 1H - Analog module

2702911

<https://www.phoenixcontact.com/us/products/2702911>

Block diagram



Internal wiring of the terminal points

# AXL F SGI2 1H - Analog module



2702911

<https://www.phoenixcontact.com/us/products/2702911>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2702911>



**cULus Listed**

Approval ID: E238705

# AXL F SGI2 1H - Analog module



2702911

<https://www.phoenixcontact.com/us/products/2702911>

## Classifications

### ECLASS

ECLASS-13.0	27242601
ECLASS-15.0	27242601

### ETIM

ETIM 10.0	EC001596
-----------	----------

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

# AXL F SGI2 1H - Analog module



2702911

<https://www.phoenixcontact.com/us/products/2702911>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	08552bd1-fe4e-4dc3-840d-be3298024436

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)