

BL FPM 21.5 - Monitor



2400515

<https://www.phoenixcontact.com/us/products/2400515>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



IP65-rated, 21.5-inch, flat panel LCD monitor with projected capacitive touch screen

Product description

The Basicline BL FPM 21.5 is an industrial flat-panel monitor that can be used in applications where a remote display location is required.

Your advantages

- 21.5" display
- DisplayPort 1.2, VGA, and DVI-I input ports
- Integrated configuration buttons
- Ambient operating temperatures from -10 °C ... 60 °C
- 21.5" touch screen display

Commercial data

Item number	2400515
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR12
Product key	DRBABD
GTIN	4055626076201
Weight per piece (including packing)	10.826 kg
Weight per piece (excluding packing)	7 kg
Customs tariff number	85299020
Country of origin	TW

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Monitor
--------------	---------

Computer data

Processor	without processor
Operating system	without operating system
RAM	without RAM
Data storage system	without data storage
Cooling	passive
Slots	without slots
Optical drive	without drive
Extras	without

Display

Display type	54.6 cm / 21.5"-TFT
Screen resolution	1920 x 1080 Pixel(s) (Full HD)
Touch technology	projective-capacitive, ten-touch control
Display lighting type	LED
Brightness	300 cd/m ² , typical (adjustable)
MTBF	> 50000 h
Color spectrum	16.7 million colors

Electrical properties

Supply

Supply voltage	24 V DC (±10 %)
Power supply unit	24 V DC
Max. current consumption	0.9 A

Connection data

Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Stripping length	7 mm

Interfaces

Interfaces	1x USB Type A (For touch control only) 1x DisplayPort
------------	--

BL FPM 21.5 - Monitor



2400515

<https://www.phoenixcontact.com/us/products/2400515>

Monitor output	1x DVI-D
	1x VGA
Network	without network

Dimensions

External dimensions

Width / Height / Depth	562 mm / 382 mm / 51 mm
------------------------	-------------------------

Installation dimensions

Width / Height / Installation depth	547 mm / 367 mm /
-------------------------------------	-------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 75 °C
Permissible humidity (operation)	10 % ... 90 % (non-condensing)
Shock	15g, 11 ms impulse
Vibration (operation)	1g

Mounting

Mounting type	Front mounting
	VESA holder
Holder system	VESA MIS-D 100 C

BL FPM 21.5 - Monitor



2400515

<https://www.phoenixcontact.com/us/products/2400515>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2400515>



UL Listed

Approval ID: E238705



cUL Listed

Approval ID: E238705



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00389

BL FPM 21.5 - Monitor



2400515

<https://www.phoenixcontact.com/us/products/2400515>

Classifications

ECLASS

ECLASS-13.0	19200201
ECLASS-15.0	19200201

ETIM

ETIM 10.0	EC004862
-----------	----------

UNSPSC

UNSPSC 21.0	43211900
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	cf7bdc86-e1c6-4116-b823-0f7c3e8a04ea