

# AXL F SGI2 1H - Analog module



2702911

<https://www.phoenixcontact.com/us/products/2702911>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Axioline F, Strain gauge capture module, transmission speed in the local bus: 100 Mbps, degree of protection: IP20, including bus base module and Axioline F connectors

## Product description

The module is designed for use within an Axioline F station. Used to evaluate strain gauges that may be located in weighing cells or load cells, for example. You can connect the strain gauges using 6- or 4-conductor technology.

## Your advantages

- 2 high-precision inputs for strain gauges
- Measuring ranges adjusted with nominal characteristic values upon delivery
- Manual entry of characteristic values
- Process data update can be parameterized in increments between 200  $\mu$ s and 100 ms
- Path adjustment in the process environment
- 2-point adjustment
- Connection of strain gauges in 6- and 4-conductor technology
- Advanced wire-break detection
- Sensor supply of up to 115 mA (8 load cells with 350  $\Omega$  per channel)
- Per channel: low-resistance, floating N/O contact
- The channels are parameterized independently of one another via the bus system
- Tara device

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2702911       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DR02          |
| Product key                          | DRI244        |
| GTIN                                 | 4055626459288 |
| Weight per piece (including packing) | 181.5 g       |
| Weight per piece (excluding packing) | 181.5 g       |
| Customs tariff number                | 85389091      |
| Country of origin                    | DE            |

# AXL F SGI2 1H - Analog module

2702911

<https://www.phoenixcontact.com/us/products/2702911>

## Technical data

### Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Width               | 35 mm  |
| Height              | 126.1 mm   |
| Depth               | 54 mm  |
| Note on dimensions  | The depth applies when a TH 35-7.5 DIN rail is used (in accordance with EN 60715). |

### Notes

#### Note on application

|                     |                         |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

### Material specifications

|                 |                 |
|-----------------|-----------------|
| Color (Housing) | gray (RAL 7042) |
|-----------------|-----------------|

### Interfaces

#### Axioline F local bus

|                      |                 |
|----------------------|-----------------|
| Number of interfaces | 2               |
| Connection method    | Bus base module |
| Transmission speed   | 100 Mbps        |

### System properties

#### Programming data (LocalbusSlave)

|                     |         |
|---------------------|---------|
| Input address area  | 12 Byte |
| Output address area | 12 Byte |

#### Fieldbus data telegram

|                             |         |
|-----------------------------|---------|
| Required parameter data     | 48 Byte |
| Required configuration data | 7 Byte  |

### Input data

#### Analog

|                          |  |
|--------------------------|--|
| Description of the input | Input channels for strain gauge          |
| Number of inputs         | 2  |
| Connection technology    | 6 or 4-wire, twisted pair shielded cable |

# AXL F SGI2 1H - Analog module



2702911

<https://www.phoenixcontact.com/us/products/2702911>

|                               |  |
|-------------------------------|--|
| Bridge difference $U_d$       | Measuring range specified by selecting the characteristic<br>-35 mV ... +35 mV |
| Bridge voltage $U_0$          | 5 V  |
| Measured value representation | 32 bits  |
| Characteristics               | can be parameterized: 350 $\mu$ V/V ... 6500 $\mu$ V/V                         |

## Contacts

|                       |  |
|-----------------------|--|
| Description           | Floating N/O contact                             |
| Quantity              | 2 ( $K_{a1}$ - $K_{b1}$ , $K_{a2}$ - $K_{b2}$ )  |
| Contact resistance    | < 1 $\Omega$ (typical)<br>< 3 $\Omega$ (maximum) |
| Typical response time | typ. 0.2 ms (opening)<br>typ. 2 ms (close)       |

## Output data

### Analog

|                    |                             |
|--------------------|-----------------------------|
| Output description | Jumper supply               |
| Number of outputs  | 2                           |
| Impedance          | > 43 $\Omega$ (per channel) |
| Output voltage     | typ. 5 V                    |
| Output current     | max. 115 mA (per channel)   |

## Product properties

|                   |   |
|-------------------|---|
| Product type      | I/O component                                       |
| Product family    | Axioline F  |
| Type              | block modular                                       |
| Mounting position | any (no temperature derating)                       |
| Scope of supply   | including bus base module and Axioline F connectors |
| Operating mode    | Process data mode with 6 words                      |

## Electrical properties

|   |        |
|---|--------|
| Maximum power dissipation for nominal condition | 1.85 W |
|---|--------|

### Potentials: Axioline F local bus supply ( $U_{BUS}$ )

|                |                              |
|----------------|------------------------------|
| Supply voltage | 5 V DC (via bus base module) |
| Current draw   | max. 75 mA<br>typ. 65 mA     |

### Potentials: Supply for analog modules ( $U_A$ )

|                      |  |
|----------------------|--|
| Supply voltage       | 24 V DC  |
| Supply voltage range | 19.2 V DC ... 30 V DC (including all tolerances, including ripple)   |
| Current draw         | typ. 110 mA (with maximum load: 8 weighing cells with 350 $\Omega$ per channel)<br>typ. 25 mA (with typical load: 1 weighing cell with 350 $\Omega$ , only one channel loaded) |

# AXL F SGI2 1H - Analog module



2702911

<https://www.phoenixcontact.com/us/products/2702911>

|                    |  |
|--------------------|--|
|                    | typ. 55 mA (with maximum load: 8 weighing cells with 350 Ω, only one channel loaded) |
| Protective circuit | Surge protection; Suppressor diode   |
|                    | Reverse polarity protection; Polarity protection diode                               |

## Electrical isolation/isolation of the voltage ranges

|   |                        |
|---|------------------------|
| Test voltage: Logic   | 500 V AC, 50 Hz, 1 min |
| Test voltage: 24 V supply (I/O)                             | 500 V AC, 50 Hz, 1 min |
| Test voltage: Analog inputs                                 | 500 V AC, 50 Hz, 1 min |
| Test voltage: N/O contact K <sub>a1</sub> - K <sub>b1</sub> | 500 V AC, 50 Hz, 1 min |
| Test voltage: N/O contact K <sub>a2</sub> - K <sub>b2</sub> | 500 V AC, 50 Hz, 1 min |
| Test voltage: Functional ground                             | 500 V AC, 50 Hz, 1 min |

## Connection data

### Connection technology

|                               |   |
|-------------------------------|---|
| Connection name               | Axioline F connector  |
| Note on the connection method | Please observe the information provided on conductor cross-sections in the "Axioline F: system and installation" user manual. |
|                               | Applications with UL approval: only use copper conductors.  |

### Axioline F connector

|                                   |   |
|-----------------------------------|---|
| Connection method                 | Push-in connection  |
| Note on the connection method     | Please observe the information provided on conductor cross-sections in the "Axioline F: system and installation" user manual. |
|                                   | Applications with UL approval: only use copper conductors.  |
| Conductor cross-section, rigid    | 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>   |
| Conductor cross-section, flexible | 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>   |
| Conductor cross-section AWG       | 24 ... 16   |
| Stripping length                  | 8 mm  |

## Environmental and real-life conditions

### Ambient conditions

|  |   |
|--|---|
| Ambient temperature (operation)          | -25 °C ... 60 °C                                  |
| Degree of protection                     | IP20  |
| Air pressure (operation)                 | 70 kPa ... 106 kPa (up to 3000 m above sea level) |
| Air pressure (storage/transport)         | 70 kPa ... 106 kPa (up to 3000 m above sea level) |
| Ambient temperature (storage/transport)  | -40 °C ... 85 °C                                  |
| Permissible humidity (operation)         | 5 % ... 95 % (non-condensing)                     |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing)                     |

### Mechanical test

|  |     |
|--|-----|
| Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6 | 5g  |
| Shock in accordance with EN 60068-2-27/IEC 60068-2-27              | 30g |
| Continuous shock in accordance with EN 60068-2-27/IEC 60068-2-27   | 10g |

# AXL F SGI2 1H - Analog module



2702911

<https://www.phoenixcontact.com/us/products/2702911>

## Standards and regulations

|                  |                                       |
|------------------|---------------------------------------|
| Protection class | III (IEC 61140, EN 61140, VDE 0140-1) |
|------------------|---------------------------------------|

## Mounting

|                   |                               |
|-------------------|-------------------------------|
| Mounting type     | DIN rail mounting             |
| Mounting position | any (no temperature derating) |

# AXL F SGI2 1H - Analog module

2702911


<https://www.phoenixcontact.com/us/products/2702911>

## Drawings

Dimensional drawing



Connection diagram




# AXL F SGI2 1H - Analog module

2702911

<https://www.phoenixcontact.com/us/products/2702911>

Connection diagram




Connection of several strain gauges in 6-conductor technology

# AXL F SGI2 1H - Analog module

2702911

<https://www.phoenixcontact.com/us/products/2702911>

Block diagram



Internal wiring of the terminal points

# AXL F SGI2 1H - Analog module

2702911

<https://www.phoenixcontact.com/us/products/2702911>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2702911>



**cULus Listed**

Approval ID: E238705

# AXL F SGI2 1H - Analog module



2702911

<https://www.phoenixcontact.com/us/products/2702911>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27242601 |
| ECLASS-15.0 | 27242601 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001596 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 32151600 |
|-------------|----------|

# AXL F SGI2 1H - Analog module



2702911

<https://www.phoenixcontact.com/us/products/2702911>

## Environmental product compliance

### EU RoHS

|   |              |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 08552bd1-fe4e-4dc3-840d-be3298024436 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)