

# FL MC EF 660 SCRJ - FO converters



2702944

<https://www.phoenixcontact.com/us/products/2702944>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



FO converter, for converting 100Base-T to polymer and PCF fiber (660 nm), SC-RJ FO connection (PROFINET standard), can be mounted on a DIN rail, 24 V DC supply

## Product description

Optical transmission with FO technology provides superior immunity to interference at maximum transmission ranges without restricting the transmission bandwidth. You can therefore replace wear-sensitive and maintenance-intensive connections and reduce downtimes in your systems.

## Your advantages

- Link fault pass through (LFPT) function for easy connection monitoring
- Very low delay times
- Mounting on a DIN rail
- Backplane bus contact, enabling alternative or redundant 24 V power supply

## Commercial data

Item number	2702944
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN06
Product key	DNC311
GTIN	4055626431260
Weight per piece (including packing)	172.7 g
Weight per piece (excluding packing)	172.7 g
Customs tariff number	85176200
Country of origin	DE

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Media converter
MTTF	929 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	461 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%)
	204 Years (SN 29500 standard, temperature 40°C, operating cycle 100%)

### Electrical properties

Electrical isolation	VCC // Ethernet
Maximum power dissipation for nominal condition	2.4 W
Test voltage data interface/power supply	1.5 kV <sub>rms</sub> (50 Hz, 1 min.)
	1500 V

### Supply

Supply voltage range	18 V DC ... 32 V DC (via pluggable COMBICON screw terminal block)
	18 V DC ... 32 V DC (as an alternative or redundant, via backplane bus contact and system current supply)
Typical current consumption	≤ 85 mA (24 V DC)
Max. current consumption	100 mA (24 V DC)
Protective circuit	Reverse polarity protection

### Output data

#### Switching

Output name	Relay output
Number of outputs	2
Contact switching type	N/O contact
Maximum switching voltage	60 V AC/DC
Max. switching current	1 A

### Connection data

#### Supply

Connection method	Plug-in screw terminal block (COMBICON), redundancy possible
Tightening torque	0.56 Nm ... 0.79 Nm

### Interfaces

# FL MC EF 660 SCRJ - FO converters



2702944

<https://www.phoenixcontact.com/us/products/2702944>

Signal	Ethernet
	PROFINET

## Data: optical FO

Transmit capacity, minimum	min. -8 dBm (980/1000 µm, static)
	min. -19 dBm (200/230 µm, static)
Transmit capacity, maximum	max. -2 dBm (980/1000 µm, static)
	max. -11 dBm (200/230 µm, static)
Transmission length incl. 3 dB system reserve	50 m (Polymer fiber with F-P 980/1000 230 dB/km)
	100 m (PCF fiber with F-K 200/230 8 dB/km)
Connection method	SC-RJ
Wavelength	660 nm
Minimum receiver sensitivity	-23 dBm (980/1000 µm, static)
	-26.8 dBm (200/230 µm, static)
Transmission medium	Polymer fiber
	PCF fiber

## Data: Ethernet interface, 100Base-T(X) in accordance with IEEE 802.3

Transmission speed	100 Mbps
Connection method	RJ45 jack, shielded
No. of channels	1
Transmission length	100 m (shielded twisted pair)
Transmission medium	Copper
Link through	Link fault pass through

## Dimensions

Dimensional drawing	
Width	22.5 mm
Height	99 mm
Depth	114.5 mm

## Material specifications

Color (Housing)	green (RAL 6021)
Material (Housing)	PA V0

## Cable/line

### FO cable

Fiber types	980/1000 µm
	200/230 µm

2702944

<https://www.phoenixcontact.com/us/products/2702944>

	Polymer fiber
	PCF fiber

## Mechanical tests

Free fall in accordance with IEC 60068-2-32	: 1 m
Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	: 5g, 150 Hz, 1.5 h, in XYZ direction
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	: 15g, 11 ms period, half-sine shock pulse

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Altitude	≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation)
Permissible humidity (operation)	10 % ... 95 % (non-condensing)

## Approvals

### CE

Certificate	CE-compliant
-------------	--------------

### Corrosive gas test

Identification	ISA-S71.04-1985 G3 Harsh Group A
----------------	----------------------------------

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	---

### Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

### Electrostatic discharge

Contact discharge	± 6 kV (Test Level 3)
Discharge in air	± 8 kV (Test Level 3)
Indirect discharge	± 6 kV
Comments	Criterion B

### Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

### Electromagnetic HF field

Frequency range	80 MHz ... 3 GHz (Test Level 3)
Field intensity	10 V/m
Comments	Criterion A

### Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

# FL MC EF 660 SCRJ - FO converters



2702944

<https://www.phoenixcontact.com/us/products/2702944>

## Fast transients (burst)

Input	± 2.2 kV (1 minute)
Signal	± 2.2 kV (1 minute)
Comments	Criterion B

## Surge current load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

## Surge current load (surge)

Input	± 0.5 kV (Supply)
Signal	± 1 kV (Shielded cable)
Comments	Criterion B

## Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

## Conducted interference

Frequency range	0.15 MHz ... 80 MHz
Comments	Criterion A
Voltage	10 V

## Emitted interference

Standards/regulations	EN 61000-6-4
Comments	Class A, industrial applications

## Criteria

Criterion A	Normal operating behavior within the specified limits.
Criterion B	Temporary impairment to operational behavior that is corrected by the device itself.

## Standards and regulations

Free from substances that could impair the application of coating	VDMA 24364:2018-05
---	--------------------

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# FL MC EF 660 SCRJ - FO converters


2702944

<https://www.phoenixcontact.com/us/products/2702944>



## Drawings

Dimensional drawing



Slim design


# FL MC EF 660 SCRJ - FO converters



2702944

<https://www.phoenixcontact.com/us/products/2702944>

Schematic diagram




Function elements

# FL MC EF 660 SCRJ - FO converters

2702944

<https://www.phoenixcontact.com/us/products/2702944>

Schematic diagram



Connect the SC-RJ plug


# FL MC EF 660 SCRJ - FO converters



2702944

<https://www.phoenixcontact.com/us/products/2702944>

## Schematic diagram




Signal direction for the fiber connection

# FL MC EF 660 SCRJ - FO converters

2702944

<https://www.phoenixcontact.com/us/products/2702944>

Schematic diagram



Switch to activate LFPT


# FL MC EF 660 SCRJ - FO converters



2702944

<https://www.phoenixcontact.com/us/products/2702944>

Block diagram



# FL MC EF 660 SCRJ - FO converters



2702944

<https://www.phoenixcontact.com/us/products/2702944>

## Classifications

### ECLASS

ECLASS-13.0

19170411

### ETIM

ETIM 9.0

EC001467

### UNSPSC

UNSPSC 21.0

43223323

2702944

<https://www.phoenixcontact.com/us/products/2702944>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	e5b45f75-6580-4bc8-a0f2-6e9cb96682c4

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)