

# TP105AT/732000 S00001 - Touch panel



2400815

<https://www.phoenixcontact.com/us/products/2400815>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Touch panel, 26.4 cm / 10.4"-TFT display (analog resistive (polyester)), 800 x 600 pixel(s) (SVGA), 65536 colors, Arm9™, 200 MHz, 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows® CE 5.0, TSvisRT, MPI.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2400815       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Product key                          | DRCABB        |
| GTIN                                 | 4055626097381 |
| Weight per piece (including packing) | 1,800 g       |
| Weight per piece (excluding packing) | 1,800 g       |
| Country of origin                    | DE            |

# TP105AT/732000 S00001 - Touch panel



2400815

<https://www.phoenixcontact.com/us/products/2400815>

## Technical data

### Product properties

|              |                |
|--------------|----------------|
| Product type | Operator panel |
|--------------|----------------|

### Computer data

|                     |                  |
|---------------------|------------------|
| Processor           | Arm9™, 200 MHz   |
| Operating system    | Windows® CE 5.0  |
| RAM                 | 64 MB SDRAM      |
|                     | 512 KB SRAM      |
| Data storage system | NOR-Flash, 32 MB |

### Display

|                       |  |
|-----------------------|--|
| Display type          | 26.4 cm / 10.4"-TFT                        |
| Screen resolution     | 800 x 600 Pixel(s) (SVGA)                  |
| Touch technology      | analog resistive (polyester)               |
| Display lighting type | LED  |
| Brightness            | 340 cd/m <sup>2</sup> typical (adjustable) |
| MTBF                  | 50000 h                                    |
| Color spectrum        | 65536 colors                               |
| Reading angle left    | 70.00 °                                    |
| Reading angle right   | 70.00 °                                    |
| Reading angle top     | 50.00 °                                    |
| Reading angle bottom  | 60.00 °                                    |

### Interfaces

|                     |                                  |
|---------------------|----------------------------------|
| Interfaces          | 2x USB Host 2.0                  |
| Optional interfaces | none                             |
| Network             | 1 x Ethernet (10/100 Mbps), RJ45 |
| Bus system          | MPI                              |

### System properties

|               |         |
|---------------|---------|
| User software | TSvisRT |
|---------------|---------|

### Electrical properties

|                         |                   |
|-------------------------|-------------------|
| Service life of battery | 5 years (typical) |
|-------------------------|-------------------|

### Supply

|                             |               |
|-----------------------------|---------------|
| Power supply unit           | 24 V DC ±20 % |
| Typical current consumption | 0.6 A         |

### Real-time clock

|                |     |
|----------------|-----|
| Realtime clock | Yes |
|----------------|-----|

### Mounting

|               |                |
|---------------|----------------|
| Mounting type | Front mounting |
|---------------|----------------|

# TP105AT/732000 S00001 - Touch panel



2400815

<https://www.phoenixcontact.com/us/products/2400815>

## Material specifications

|                      |                             |
|----------------------|-----------------------------|
| Material front plate | Aluminum (natural anodized) |
| Housing material     | Steel sheet, zinc-plated    |

## Environmental and real-life conditions

### Ambient conditions

|   |                                      |
|---|--------------------------------------|
| Degree of protection                    | IP65 (front), IP20 (back)<br>NEMA 4X |
| Ambient temperature (operation)         | 0 °C ... 50 °C                       |
| Ambient temperature (storage/transport) | -25 °C ... 70 °C                     |
| Altitude                                | 3000 m                               |
| Permissible humidity (operation)        | 20 % ... 85 %                        |
| Shock                                   | 15g, according to IEC 60068-2-27     |
| Vibration (operation)                   | 1g, according to EN 60068-2-6        |

## Dimensions

### External dimensions

|                        |  |
|------------------------|--|
| Width / Height / Depth | 295 mm / 220 mm / 5 mm (Dimensions of the front plate) |
|------------------------|--|

### Installation dimensions

|                                     |   |
|-------------------------------------|---|
| Width / Height / Installation depth | 287 mm / 212 mm / 67 mm (Mounting cutout, depth with bus if bus system present in the device) |
|-------------------------------------|---|

# TP105AT/732000 S00001 - Touch panel



2400815

<https://www.phoenixcontact.com/us/products/2400815>

## Classifications

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 43211904 |
|-------------|----------|

2400815

<https://www.phoenixcontact.com/us/products/2400815>

## Environmental product compliance

### EU RoHS

|   |   |
|---|---|
| Fulfills EU RoHS substance requirements | Yes   |
| Exemption                               | 6(a), 6(a)-I, 6(b), 6(b)-II, 6(c), 7(a), 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-15   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                      |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)