

# ME 45 UTG GYWH - Mounting base housing



2707123

<https://www.phoenixcontact.com/us/products/2707123>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Component housing, Tall design, without vents, width: 45 mm, depth: 99 mm, cross connection: without bus connector, number of positions cross connector: not relevant

## Your advantages

- Can be mounted on the DIN rail
- With integrated or DIN-rail-mountable bus connector as an option

## Commercial data

Item number	2707123
Packing unit	10 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ACHAAA
GTIN	4017918895495
Weight per piece (including packing)	66.08 g
Weight per piece (excluding packing)	51.004 g
Country of origin	DE

# ME 45 UTG GYWH - Mounting base housing



2707123

<https://www.phoenixcontact.com/us/products/2707123>

## Technical data

### Notes

Assembly note	Please observe the application note in the download area.
Recommendation	Material of contact pads for bus connector, galvanic gold (hard gold)

### Product properties

Product type	Lower housing part
Housing type	Component housing
Product family	ME UTG
Type	Lower housing parts without vents, housing cover necessary to complete the module
Number of positions	32
	8
Ventilation openings present	no

### Dimensions

Width	45 mm
Depth	99 mm

### Material specifications

Housing material	PA
------------------	----

### Environmental and real-life conditions

#### Power dissipation single housing for 20 °C

Ambient temperature	20 °C
Reduction factor	1
Mounting position	vertical
Power dissipation	7.6 W

#### Power dissipation single housing for 30 °C

Ambient temperature	30 °C
Reduction factor	0.91
Mounting position	vertical
Power dissipation	6.9 W

#### Power dissipation single housing for 40 °C

Ambient temperature	40 °C
Reduction factor	0.81
Mounting position	vertical
Power dissipation	6.1 W

#### Power dissipation single housing for 50 °C

Ambient temperature	50 °C
---------------------	-------

# ME 45 UTG GYWH - Mounting base housing



2707123

<https://www.phoenixcontact.com/us/products/2707123>

Reduction factor	0.7
Mounting position	vertical
Power dissipation	5.3 W

## Power dissipation single housing for 60 °C

Ambient temperature	60 °C
Reduction factor	0.57
Mounting position	vertical
Power dissipation	4.3 W

## Power dissipation single housing for 70 °C

Ambient temperature	70 °C
Reduction factor	0.49
Mounting position	vertical
Power dissipation	3.7 W

## Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.15 mm (10 Hz ... 58.1 Hz)
Acceleration	2g (58.1 Hz ... 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis

## Glow-wire test

Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

## Thermal stability / ball thrust test

Specification	IEC 60695-10-2:2014-02
Temperature	125 °C
Test duration	1 h
Force	20 N

## Mechanical strength / tumbling barrel

Specification	IEC 60998-1:2002-12
Height of fall	50 cm
Frequency	10

## Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Half-sine
Acceleration	15g
Shock duration	11 ms
Number of shocks per direction	3

# ME 45 UTG GYWH - Mounting base housing



2707123

<https://www.phoenixcontact.com/us/products/2707123>

Test directions	X-, Y- and Z-axis (pos. and neg.)
Degree of protection (IP code)	
Specification	IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08
Ambient conditions	
Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C

# ME 45 UTG GYWH - Mounting base housing

2707123

<https://www.phoenixcontact.com/us/products/2707123>



## Classifications

### ECLASS

ECLASS-15.0	27190601
-------------	----------

# ME 45 UTG GYWH - Mounting base housing



2707123

<https://www.phoenixcontact.com/us/products/2707123>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)