

# MSTBO 2,5/ 4-4 ST SET - Connector set



2707961

<https://www.phoenixcontact.com/us/products/2707961>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Set, consisting of COMBICON headers and PCB terminal blocks for 6 x 4-pos. (24-pos.), color: green



## Commercial data

Item number	2707961
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AC08
Product key	ACHADB
GTIN	4017918906092
Weight per piece (including packing)	38.3 g
Weight per piece (excluding packing)	36.74 g
Customs tariff number	85366990
Country of origin	DE

# MSTBO 2,5/ 4-4 ST SET - Connector set

2707961

<https://www.phoenixcontact.com/us/products/2707961>

## Set consists of

### MSTBO 2,5/ 4-G1L - PCB header

1861060

<https://www.phoenixcontact.com/us/products/1861060>



PCB headers, nominal cross section: 2.5 mm<sup>2</sup>, color: green, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Sn, contact connection type: Pin, number of potentials: 4, number of rows: 1, number of positions: 4, number of connections: 4, product range: MSTBO 2,5/..-G1L, pitch: 5 mm, mounting: Wave soldering, pin layout: Linear pinning, solder pin [P]: 3.5 mm, number of solder pins per potential: 1, Pin connector pattern alignment: Orthogonal, locking: without, type of packaging: packed in cardboard, Product with pin output on left side

### MSTBO 2,5/ 4-G1R - PCB header

1861073

<https://www.phoenixcontact.com/us/products/1861073>



PCB headers, nominal cross section: 2.5 mm<sup>2</sup>, color: green, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Sn, contact connection type: Pin, number of potentials: 4, number of rows: 1, number of positions: 4, number of connections: 4, product range: MSTBO 2,5/..-G1R, pitch: 5 mm, mounting: Wave soldering, pin layout: Linear pinning, solder pin [P]: 3.5 mm, number of solder pins per potential: 1, Pin connector pattern alignment: Orthogonal, locking: without, type of packaging: packed in cardboard, Product with pin output on right side

# MSTBO 2,5/ 4-4 ST SET - Connector set

2707961

<https://www.phoenixcontact.com/us/products/2707961>



## MSTBT 2,5/ 4-ST - PCB connector

1779851

<https://www.phoenixcontact.com/us/products/1779851>



PCB connector, nominal cross section: 2.5 mm<sup>2</sup>, color: green, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Sn, contact connection type: Socket, number of potentials: 4, number of rows: 1, number of positions: 4, number of connections: 4, product range: MSTBT 2,5/..-ST, pitch: 5 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, conductor/PCB connection direction: 0 °, locking clip: - Locking clip, plug-in system: COMBICON MSTB 2,5, locking: without, mounting method: without, type of packaging: packed in cardboard

# MSTBO 2,5/ 4-4 ST SET - Connector set



2707961

<https://www.phoenixcontact.com/us/products/2707961>

## Technical data

### Product properties

Product type	Connector set
Number of positions	4
Pitch	5 mm
Mounting type	without
Pin layout	Linear pinning

### Electrical properties

Rated voltage (II/2)	400 V
Rated voltage (III/2)	320 V
Rated surge voltage (II/2)	4 kV
Rated surge voltage (III/2)	4 kV
Rated surge voltage (III/3)	4 kV

### Dimensions

Pitch	5 mm
-------	------

### Material specifications

Color (Housing)	green (RAL 6021)
Insulating material	PA
Contact surface material	Sn

### Mounting

Mounting type	Soldering
Pin layout	Linear pinning

# MSTBO 2,5/ 4-4 ST SET - Connector set



2707961

<https://www.phoenixcontact.com/us/products/2707961>

## Classifications

### ECLASS

ECLASS-13.0

27460201

### ETIM

ETIM 9.0

EC002637

### UNSPSC

UNSPSC 21.0

39121400

# MSTBO 2,5/ 4-4 ST SET - Connector set



2707961

<https://www.phoenixcontact.com/us/products/2707961>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	d0eef2c8-8f7a-4149-89c0-6f2cdae8eb33

### EF3.1 Climate Change

CO2e kg	0.162 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)