

# PSI-MOS-RS422/FO 850 E/E2000 - FO converters



2708012

<https://www.phoenixcontact.com/us/products/2708012>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



FO converter for INTERBUS up to 2 Mbps, two relay contacts, terminal device with one FO interface (E2000 duplex) in 850 nm technology, for PCF/fiberglass cable (multimode)

## Commercial data

Item number	2708012
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DNC216
GTIN	4046356078979
Weight per piece (including packing)	162 g
Weight per piece (excluding packing)	159.6 g
Country of origin	DE

## Technical data

### Product properties

Product type	Media converter
MTBF	756 Years (Telcordia standard, 25°C temperature, 21% operating cycle (5 days a week, 8 hours a day))
	152 Years (Telcordia standard, 40°C temperature, 34.25% operating cycle (5 days a week, 12 hours a day))

### Connection data

#### Supply

Tightening torque	0.56 Nm ... 0.79 Nm
-------------------	---------------------

### Interfaces

Signal	INTERBUS
--------	----------

#### Data: optical FO

Transmission length incl. 3 dB system reserve	2200 m (F-K 200/230 8 dB/km with quick mounting connector)
	5800 m (with F-G 50/125 2.5 dB/km)
	5000 m (with F-G 62,5/125 3.0 dB/km)
Connection method	E2000
Wavelength	850 nm
Transmission medium	PCF fiber
	Multi-mode fiberglass

#### Data

Transmission medium	Copper
---------------------	--------

### Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	Vibration (operation): 5g, 10...150 Hz, 2.5 h, in XYZ direction
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	Shock (operation): 15g, 11 ms period, half-sine shock pulse

### Environmental and real-life conditions

#### Ambient conditions

Altitude	≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation)
----------	--

### Approvals

#### Corrosive gas test

Identification	ISA-S71.04-1985 G3 Harsh Group A
----------------	----------------------------------

# PSI-MOS-RS422/FO 850 E/E2000 - FO converters



2708012

<https://www.phoenixcontact.com/us/products/2708012>

## Classifications

### UNSPSC

UNSPSC 21.0	43223323
-------------	----------

2708012

<https://www.phoenixcontact.com/us/products/2708012>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)