

TP151XIT-10/3101C240 S00054 - Touch panel



2400974

<https://www.phoenixcontact.com/us/products/2400974>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Touch panel, 38.1 cm / 15"-TFT display (analog resistive (polyester)), 1024 x 768 pixel(s) (XGA), 262144 colors, Xscale® PXA320, 806 MHz, 2x USB host 1.1, 1 x Ethernet (10/100 Mbps), RJ45, Windows® CE 6.0, Visu+, without bus system.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2400974 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Product key | DRCABC |
| GTIN | 4055626105024 |
| Weight per piece (including packing) | 3,600 g |
| Weight per piece (excluding packing) | 3,600 g |
| Country of origin | DE |

Technical data

Notes

Utilization restriction

| | |
|----------|---|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---|

Product properties

| | |
|--------------|----------------|
| Product type | Operator panel |
|--------------|----------------|

Computer data

| | |
|---------------------|---------------------------|
| Processor | Xscale® PXA320, 806 MHz |
| Operating system | Windows® CE 6.0 |
| RAM | 128 MB SDRAM 1 MB SRAM |
| Data storage system | NAND-Flash, 1 GB |

Display

| | |
|-----------------------|--|
| Display type | 38.1 cm / 15"-TFT |
| Screen resolution | 1024 x 768 Pixel(s) (XGA) |
| Touch technology | analog resistive (polyester) |
| Display lighting type | LED |
| Brightness | 480 cd/m ² typical (adjustable) |
| MTBF | 50000 h |
| Color spectrum | 262144 colors |
| Reading angle left | 80.00 ° |
| Reading angle right | 80.00 ° |
| Reading angle top | 65.00 ° |
| Reading angle bottom | 80.00 ° |

Interfaces

| | |
|---------------------|----------------------------------|
| Interfaces | 2x USB host 1.1 |
| Optional interfaces | CF slot |
| Network | 1 x Ethernet (10/100 Mbps), RJ45 |
| Bus system | without bus system |

System properties

| | |
|---------------|-------|
| User software | Visu+ |
|---------------|-------|

Electrical properties

| | |
|-------------------------|-------------------|
| Service life of battery | 5 years (typical) |
|-------------------------|-------------------|

Real-time clock

| | |
|----------------|-----|
| Realtime clock | Yes |
|----------------|-----|

TP151XIT-10/3101C240 S00054 - Touch panel



2400974

<https://www.phoenixcontact.com/us/products/2400974>

Supply

| | |
|-------------------|--------------------|
| Power supply unit | 24 V DC \pm 20 % |
|-------------------|--------------------|

Mounting

| | |
|---------------|----------------|
| Mounting type | Front mounting |
|---------------|----------------|

Material specifications

| | |
|----------------------|-----------------------------|
| Material front plate | Aluminum (natural anodized) |
| Housing material | Steel sheet, zinc-plated |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--------------------------------------|
| Degree of protection | IP65 (front), IP20 (back) NEMA 4X |
| Ambient temperature (operation) | 0 °C ... 50 °C |
| Ambient temperature (storage/transport) | -25 °C ... 70 °C |
| Altitude | 3000 m |
| Permissible humidity (operation) | 20 % ... 85 % |
| Shock | 15g, according to IEC 60068-2-27 |
| Vibration (operation) | 1g, according to EN 60068-2-6 |

Dimensions

External dimensions

| | |
|------------------------|--|
| Width / Height / Depth | 400 mm / 329 mm / 5 mm (Dimensions of the front plate) |
|------------------------|--|

Installation dimensions

| | |
|-------------------------------------|---|
| Width / Height / Installation depth | 373 mm / 302 mm / 65 mm (Mounting cutout, depth with bus if bus system present in the device) |
|-------------------------------------|---|

2400974

<https://www.phoenixcontact.com/us/products/2400974>

Environmental product compliance

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-15 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
|--|--|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com