

# TP21AM/782000 S00001 - Touch panel



2401022

<https://www.phoenixcontact.com/us/products/2401022>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Touch panel, 14.5 cm / 5.7"-FSTN display (analog resistive (polyester)), 320 x 240 pixel(s) (QVGA), 5 grayscales, Arm9™, 200 MHz, 2x USB Host 2.0, 1x COM (RS-232/485), 1 x Ethernet (10/100 Mbps), RJ45, Windows® CE 5.0, TSvisRT, without bus system.

## Commercial data

Item number	2401022
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRCABB
GTIN	4055626097022
Weight per piece (including packing)	680 g
Weight per piece (excluding packing)	680 g
Country of origin	DE

# TP21AM/782000 S00001 - Touch panel



2401022

<https://www.phoenixcontact.com/us/products/2401022>

## Technical data

### Product properties

Product type	Operator panel
--------------	----------------

### Computer data

Processor	Arm9™, 200 MHz
Operating system	Windows® CE 5.0
RAM	64 MB SDRAM
	512 KB SRAM
Data storage system	NOR-Flash, 32 MB

### Display

Display type	14.5 cm / 5.7"-FSTN
Screen resolution	320 x 240 Pixel(s) (QVGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	120 cd/m <sup>2</sup> typical (adjustable)
MTBF	40000 h
Color spectrum	5 grayscales
Reading angle left	40.00 °
Reading angle right	40.00 °
Reading angle top	45.00 °
Reading angle bottom	45.00 °

### Interfaces

Interfaces	2x USB Host 2.0
	1x COM (RS-232/485)
Optional interfaces	none
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without bus system

### System properties

User software	TSvisRT
---------------	---------

### Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

### Supply

Power supply unit	24 V DC +/- 20 %
Typical current consumption	0.25 A

### Real-time clock

Realtime clock	Yes
----------------	-----

### Mounting

# TP21AM/782000 S00001 - Touch panel



2401022

<https://www.phoenixcontact.com/us/products/2401022>

Mounting type	Front mounting
---------------	----------------

## Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65 (front), IP20 (back) NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Altitude	3000 m
Permissible humidity (operation)	20 % ... 85 %
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

## Dimensions

### External dimensions

Width / Height / Depth	203 mm / 147 mm / 5 mm (Dimensions of the front plate)
------------------------	--

### Installation dimensions

Width / Height / Installation depth	195 mm / 139 mm / 66 mm (Mounting cutout, depth with bus if bus system present in the device)
-------------------------------------	---

# TP21AM/782000 S00001 - Touch panel



2401022

<https://www.phoenixcontact.com/us/products/2401022>

## Classifications

### UNSPSC

UNSPSC 21.0	43211904
-------------	----------

2401022

<https://www.phoenixcontact.com/us/products/2401022>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(b), 6(b)-II, 6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)