TPE057AGQ/107060020 S00008 - Touch panel

2401205

https://www.phoenixcontact.com/us/products/2401205

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Rugged-Touch panel; 14.5 cm / 5.7"-TFT display (Analog resistive (GFG)); 320 x 240 pixel(s) (QVGA); 65536 colors; Processor: Arm9™, 184 MHz; Interfaces: 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45; Operating system: Windows® CE 5.0; Software: Open platform; without bus system

Commercial data

Item number	2401205
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRCACA
GTIN	4055626095998
Weight per piece (including packing)	750 g
Weight per piece (excluding packing)	750 g
Country of origin	DE

Technical data

Product properties

Product type	Operator panel
Application	Rugged

Computer data

Processor	Arm9™, 184 MHz
Operating system	Windows® CE 5.0
RAM	128 MB SDRAM
	512 KB NV
Data storage system	NOR-Flash, 64 MB

Display

Display type	14.5 cm / 5.7"-TFT
Screen resolution	320 x 240 Pixel(s) (QVGA)
Touch technology	Analog resistive (GFG)
Display lighting type	LED
Brightness	400 cd/m², typical (adjustable)
MTBF	40000 h
Color spectrum	65536 colors
Reading angle left	75.00 °
Reading angle right	75.00 °
Reading angle top	60.00 °
Reading angle bottom	75.00 °

Interfaces

Interfaces	2x USB Host 2.0
Optional interfaces	none
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without bus system

System properties

User software	Open platform

Electrical properties

Service life of battery	5 years (typical)

Supply

Typical current consumption	0.2 A

Real-time clock

Real-time clock	Yes

Supply

Power supply unit	24 V DC ±20 %

Mounting

Mounting type	Bolt fixing

Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (front), IP20 (back)
	NEMA 4X
Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 80 °C
Altitude	4000 m
Permissible humidity (operation)	5 % ... 95 % (Front)
	20 % ... 85 % (On the rear)
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Dimensions

External dimensions

Width / Height / Depth	195 mm / 153 mm / 5 mm (Dimensions of the front plate)

Installation dimensions

Width / Height / Installation depth	161 mm / 119 mm / 42 mm (Mounting cutout, depth with bus if bus system present in the device)

Classifications

UNSPSC

UNSPSC 21.0	43211904

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(b), 6(b)-II, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com