

TPE070AGW/107060020 S00001 - Touch panel



2401225

<https://www.phoenixcontact.com/us/products/2401225>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Rugged-Touch panel, 17.8 cm / 7"-TFT display (Analog resistive (GFG)), 800 x 480 pixel(s) (WVGA), 65536 colors, Arm9™, 184 MHz, 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows® CE 5.0, TSvisRT, without bus system.

Similar figure

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2401225 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Product key | DRCACB |
| GTIN | 4055626095882 |
| Weight per piece (including packing) | 1,000 g |
| Weight per piece (excluding packing) | 1,000 g |
| Country of origin | DE |

Technical data

Product properties

| | |
|--------------|----------------|
| Product type | Operator panel |
| Application | Rugged |

Computer data

| | |
|---------------------|---------------------------|
| Processor | Arm9™, 184 MHz |
| Operating system | Windows® CE 5.0 |
| RAM | 128 MB SDRAM 512 KB NV |
| Data storage system | NOR-Flash, 64 MB |

Display

| | |
|-----------------------|---------------------------------|
| Display type | 17.8 cm / 7"-TFT |
| Screen resolution | 800 x 480 Pixel(s) (WVGA) |
| Touch technology | Analog resistive (GFG) |
| Display lighting type | LED |
| Brightness | 350 cd/m², typical (adjustable) |
| MTBF | 40000 h |
| Color spectrum | 65536 colors |
| Reading angle left | 70.00 ° |
| Reading angle right | 70.00 ° |
| Reading angle top | 65.00 ° |
| Reading angle bottom | 65.00 ° |

Interfaces

| | |
|---------------------|----------------------------------|
| Interfaces | 2x USB Host 2.0 |
| Optional interfaces | none |
| Network | 1 x Ethernet (10/100 Mbps), RJ45 |
| Bus system | without bus system |

System properties

| | |
|---------------|---------|
| User software | TSvisRT |
|---------------|---------|

Electrical properties

| | |
|-------------------------|-------------------|
| Service life of battery | 5 years (typical) |
|-------------------------|-------------------|

Supply

| | |
|-----------------------------|-------|
| Typical current consumption | 0.3 A |
|-----------------------------|-------|

Real-time clock

| | |
|----------------|-----|
| Realtime clock | Yes |
|----------------|-----|

Supply

| | |
|-------------------|---------------|
| Power supply unit | 24 V DC ±20 % |
|-------------------|---------------|

TPE070AGW/107060020 S00001 - Touch panel



2401225

<https://www.phoenixcontact.com/us/products/2401225>

Mounting

| | |
|---------------|-------------|
| Mounting type | Bolt fixing |
|---------------|-------------|

Material specifications

| | |
|----------------------|-----------------------------|
| Material front plate | Aluminum (natural anodized) |
| Housing material | Steel sheet, zinc-plated |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection | IP67 (front), IP20 (back) NEMA 4X |
| Ambient temperature (operation) | -20 °C ... 70 °C |
| Ambient temperature (storage/transport) | -30 °C ... 80 °C |
| Altitude | 4000 m |
| Permissible humidity (operation) | 5 % ... 95 % (Front) 20 % ... 85 % (On the rear) |
| Shock | 15g, according to IEC 60068-2-27 |
| Vibration (operation) | 1g, according to EN 60068-2-6 |

Dimensions

External dimensions

| | |
|------------------------|--|
| Width / Height / Depth | 234 mm / 174 mm / 5 mm (Dimensions of the front plate) |
|------------------------|--|

Installation dimensions

| | |
|-------------------------------------|---|
| Width / Height / Installation depth | 200 mm / 140 mm / 65 mm (Mounting cutout, depth with bus if bus system present in the device) |
|-------------------------------------|---|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com