

# TPG070SGW/200130023 S00069 - Touch panel



2401277

<https://www.phoenixcontact.com/us/products/2401277>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Rugged-Touch panel, 17.8 cm / 7"-TFT display (Analog resistive (GFG)), 800 x 480 pixel(s) (WVGA), 16.7 million colors, Arm® Cortex®-A8, 1000 MHz, 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows® Embedded Compact 7, Open platform, without bus system.

Similar figure

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2401277       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Product key                          | DRCACA        |
| GTIN                                 | 4055626109800 |
| Weight per piece (including packing) | 1,100 g       |
| Weight per piece (excluding packing) | 1,100 g       |
| Country of origin                    | DE            |

## Technical data

### Product properties

|              |                |
|--------------|----------------|
| Product type | Operator panel |
| Application  | Rugged         |

### Computer data

|                     |                             |
|---------------------|-----------------------------|
| Processor           | Arm® Cortex®-A8, 1000 MHz   |
| Operating system    | Windows® Embedded Compact 7 |
| RAM                 | 512 MB LPDDR SDRAM          |
| Data storage system | NAND-Flash, 256 MB          |
| Slots               | 1x SD                       |

### Display

|                       |                                 |
|-----------------------|---------------------------------|
| Display type          | 17.8 cm / 7"-TFT                |
| Screen resolution     | 800 x 480 Pixel(s) (WVGA)       |
| Touch technology      | Analog resistive (GFG)          |
| Display lighting type | LED                             |
| Brightness            | 400 cd/m², typical (adjustable) |
| MTBF                  | 50000 h                         |
| Color spectrum        | 16.7 million colors             |
| Reading angle left    | 70.00 °                         |
| Reading angle right   | 70.00 °                         |
| Reading angle top     | 60.00 °                         |
| Reading angle bottom  | 60.00 °                         |

### Interfaces

|            |                                  |
|------------|----------------------------------|
| Interfaces | 2x USB Host 2.0                  |
| Network    | 1 x Ethernet (10/100 Mbps), RJ45 |
| Bus system | without bus system               |

### System properties

|               |               |
|---------------|---------------|
| User software | Open platform |
|---------------|---------------|

### Electrical properties

|                         |                   |
|-------------------------|-------------------|
| Service life of battery | 5 years (typical) |
|-------------------------|-------------------|

### Supply

|                             |               |
|-----------------------------|---------------|
| Power supply unit           | 24 V DC ±20 % |
| Typical current consumption | 0.4 A         |

### Real-time clock

|                |     |
|----------------|-----|
| Realtime clock | Yes |
|----------------|-----|

### Mounting

|               |             |
|---------------|-------------|
| Mounting type | Bolt fixing |
|---------------|-------------|

2401277

<https://www.phoenixcontact.com/us/products/2401277>

## Material specifications

|                      |                             |
|----------------------|-----------------------------|
| Material front plate | Aluminum (natural anodized) |
| Housing material     | Steel sheet, zinc-plated    |

## Environmental and real-life conditions

### Ambient conditions

|   |                                  |
|---|----------------------------------|
| Degree of protection                    | IP67 (front), IP20 (back)        |
|   | NEMA 4X                          |
| Ambient temperature (operation)         | -32 °C ... 70 °C                 |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C                 |
| Altitude                                | 3000 m                           |
| Permissible humidity (operation)        | 5 % ... 95 % (Front)             |
|   | 20 % ... 85 % (On the rear)      |
| Shock                                   | 15g, according to IEC 60068-2-27 |
| Vibration (operation)                   | 1g, according to EN 60068-2-6    |

## Dimensions

### External dimensions

|                        |  |
|------------------------|--|
| Width / Height / Depth | 234 mm / 174 mm / 5 mm (Dimensions of the front plate) |
|------------------------|--|

### Installation dimensions

|                                     |   |
|-------------------------------------|---|
| Width / Height / Installation depth | 200 mm / 140 mm / 77 mm (Mounting cutout, depth with bus if bus system present in the device) |
|-------------------------------------|---|

2401277

<https://www.phoenixcontact.com/us/products/2401277>

## Classifications

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 43211904 |
|-------------|----------|

2401277

<https://www.phoenixcontact.com/us/products/2401277>

## Environmental product compliance

### EU RoHS

|   |   |
|---|---|
| Fulfills EU RoHS substance requirements | Yes   |
| Exemption                               | 6(a), 6(a)-I, 6(b), 6(b)-II, 6(c), 7(a), 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-15   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                      |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
 586 Fulling Mill Road  
 Middletown, PA 17057, United States  
 (+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)