


# DOK 1,5-2D - Initiator/actuator terminal block



2717139

<https://www.phoenixcontact.com/us/products/2717139>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Initiator/actuator terminal block, nom. voltage: 250 V, nominal current: 24 A, connection method: Screw connection, Rated cross section: 2.5 mm<sup>2</sup>, cross section: 0.2 mm<sup>2</sup> - 4 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: gray

## Your advantages

- Same shape as DIK ... three-level initiator terminal blocks
- The forks of the insertion bridge can be easily loosened for bridging between non-adjacent terminal blocks
- Terminal blocks with red and green LEDs are available for optical signaling of the initiator and actuator wiring
- Because the spine of the insertion bridge can be snapped into place with the terminal block housing, all the terminal points can be wired freely and the bridge can be securely positioned
- Unlike the DIK terminal blocks, the lower level of these output terminal blocks makes direct contact with the DIN rail and as a PE connection are marked yellow-green
- The upper level contains the feed-through connections for the signal cable which can be labeled
- Alternate wiring of an actuator followed by an initiator is easy
- The middle level supplies the connected actuators with power

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2717139       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE12          |
| Product key                          | BE1217        |
| GTIN                                 | 4017918102111 |
| Weight per piece (including packing) | 18.14 g       |
| Weight per piece (excluding packing) | 18.14 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | PL            |

# DOK 1,5-2D - Initiator/actuator terminal block



2717139

<https://www.phoenixcontact.com/us/products/2717139>

## Technical data

### Product properties

|                       |                                |
|-----------------------|--------------------------------|
| Product type          | Sensor/actuator terminal block |
| Number of connections | 5                              |
| Number of rows        | 3                              |
| Potentials            | 3                              |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|   |        |
|---|--------|
| Rated surge voltage                             | 4 kV   |
| Maximum power dissipation for nominal condition | 0.77 W |

### Connection data

|                                 |                     |
|---------------------------------|---------------------|
| Grounding foot                  | Yes                 |
| Number of connections per level | 1                   |
| Nominal cross section           | 2.5 mm <sup>2</sup> |

### Level 1+2+3

|   |   |
|---|---|
| Connection method   | Screw connection  |
| Screw thread  | M3  |
| Tightening torque   | 0.5 ... 0.6 Nm  |
| Stripping length  | 8 mm  |
| Internal cylindrical gage   | A3  |
| Connection in acc. with standard  | IEC 60947-7-1/IEC 60947-7-2                               |
| Conductor cross-section rigid   | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>                 |
| Cross section AWG   | 24 ... 12 (converted acc. to IEC)                         |
| Conductor cross-section flexible  | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>               |
| Conductor cross-section, flexible [AWG]   | 24 ... 14 (converted acc. to IEC)                         |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>              |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>              |
| Cross-section with insertion bridge, rigid  | 4 mm <sup>2</sup>   |
| Cross-section with insertion bridge, flexible   | 2.5 mm <sup>2</sup>                                       |
| 2 conductors with same cross section, rigid   | 0.2 mm <sup>2</sup> ... 1 mm <sup>2</sup>                 |
| 2 conductors with same cross section, flexible  | 0.2 mm <sup>2</sup> ... 1 mm <sup>2</sup>                 |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve       | 0.25 mm <sup>2</sup> ... 1 mm <sup>2</sup>                |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 1 mm <sup>2</sup>                 |
| Nominal cross section   | 2.5 mm <sup>2</sup>                                       |
| Nominal current   | 24 A  |
| Maximum load current  | 26 A (with a 2.5 mm <sup>2</sup> conductor cross-section) |

# DOK 1,5-2D - Initiator/actuator terminal block



2717139

<https://www.phoenixcontact.com/us/products/2717139>

|                 |       |
|-----------------|-------|
| Nominal voltage | 250 V |
|-----------------|-------|

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 6.2 mm  |
| Height             | 62.5 mm |
| Depth on NS 35/7,5 | 54.5 mm |
| Depth on NS 35/15  | 62 mm   |

## Material specifications

|   |                 |
|---|-----------------|
| Color   | gray (RAL 7042) |
| Flammability rating according to UL 94                                  | V2              |
| Insulating material group   | I               |
| Insulating material   | PA              |
| Static insulating material application in cold                          | -60 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3     |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 28 MJ/kg        |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed          |

## Electrical tests

### Surge voltage test

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 4.8 kV      |
| Result                | Test passed |

### Temperature-rise test

|  |                                     |
|--|-------------------------------------|
| Requirement temperature-rise test                | Increase in temperature $\leq$ 45 K |
| Result   | Test passed                         |
| Short-time withstand current 2.5 mm <sup>2</sup> | 0.3 kA                              |
| Short-time withstand current 4 mm <sup>2</sup>   | 0.48 kA                             |
| Result   | Test passed                         |

### Power-frequency withstand voltage

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 1.5 kV      |
| Result                | Test passed |

## Mechanical properties

### Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

# DOK 1,5-2D - Initiator/actuator terminal block



2717139

<https://www.phoenixcontact.com/us/products/2717139>

## Mechanical tests

### Mechanical strength

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

### Attachment on the carrier

|                         |             |
|-------------------------|-------------|
| DIN rail/fixing support | NS 35       |
| Test force setpoint     | 1 N         |
| Result                  | Test passed |

### Test for conductor damage and slacking

|                                |                              |
|--------------------------------|------------------------------|
| Rotation speed                 | 10 rpm                       |
| Revolutions                    | 135                          |
| Conductor cross-section/weight | 0.2 mm <sup>2</sup> / 0.2 kg |
|                                | 2.5 mm <sup>2</sup> / 0.7 kg |
|                                | 4 mm <sup>2</sup> / 0.9 kg   |
| Result                         | Test passed                  |

## Environmental and real-life conditions

### Needle-flame test

|                  |             |
|------------------|-------------|
| Time of exposure | 30 s        |
| Result           | Test passed |

### Ambient conditions

|  |  |
|--|--|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)  |
| Ambient temperature (assembly)           | -5 °C ... 70 °C  |
| Ambient temperature (actuation)          | -5 °C ... 70 °C  |
| Permissible humidity (operation)         | 20 % ... 90 %  |
| Permissible humidity (storage/transport) | 30 % ... 70 %  |

## Standards and regulations


|                                  |                             |
|----------------------------------|-----------------------------|
| Connection in acc. with standard | IEC 60947-7-1/IEC 60947-7-2 |
|----------------------------------|-----------------------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

## Drawings

Circuit diagram




# DOK 1,5-2D - Initiator/actuator terminal block

2717139

<https://www.phoenixcontact.com/us/products/2717139>

Circuit diagram



# DOK 1,5-2D - Initiator/actuator terminal block




2717139


<https://www.phoenixcontact.com/us/products/2717139>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2717139>

|  <b>CSA</b><br>Approval ID: 13631 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
|  | 300 V                 | 15 A                  | 28 - 14           | -                           |

|  <b>EAC</b><br>Approval ID: KZ7500651131219505 |  |  |  |  |
|---|--|--|--|--|
|---|--|--|--|--|

|  <b>cULus Recognized</b><br>Approval ID: E60425 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B  |                       |                       |                   |                             |
|  | 300 V                 | 15 A                  | 30 - 14           | -                           |
| PE connection  | -                     | -                     | 30 - 14           | -                           |
| C  |                       |                       |                   |                             |
|  | 150 V                 | 15 A                  | 30 - 14           | -                           |
| PE connection  | -                     | -                     | 30 - 14           | -                           |
| D  |                       |                       |                   |                             |
|  | 150 V                 | 15 A                  | 30 - 14           | -                           |

# DOK 1,5-2D - Initiator/actuator terminal block



2717139

<https://www.phoenixcontact.com/us/products/2717139>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250112 |
| ECLASS-15.0 | 27250112 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000900 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# DOK 1,5-2D - Initiator/actuator terminal block



2717139

<https://www.phoenixcontact.com/us/products/2717139>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |             |
|---------|-------------|
| CO2e kg | 0.1 kg CO2e |
|---------|-------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)