

TP105AT/733000 S00007 - Touch panel



2401408

<https://www.phoenixcontact.com/us/products/2401408>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Touch panel, 26.4 cm / 10.4"-TFT display (analog resistive (polyester)), 800 x 600 pixel(s) (SVGA), 65536 colors, Arm9™, 200 MHz, 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows® CE 5.0, Open platform, MPI.

Similar figure

Commercial data

Item number	2401408
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRCABA
GTIN	4055626146485
Country of origin	Information on the country of origin is provided with the delivery.

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Operator panel
--------------	----------------

Computer data

Processor	Arm9™, 200 MHz
Operating system	Windows® CE 5.0
RAM	512 KB SRAM
Data storage system	NOR-Flash, 32 MB
Optional keys	without

Display

Display type	26.4 cm / 10.4"-TFT
Screen resolution	800 x 600 Pixel(s) (SVGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	340 cd/m² typical (adjustable)
MTBF	50000 h
Color spectrum	65536 colors
Reading angle left	70.00 °
Reading angle right	70.00 °
Reading angle top	50.00 °
Reading angle bottom	60.00 °

Interfaces

Interfaces	2x USB Host 2.0
Optional interfaces	none
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	MPI

System properties

User software	Open platform
---------------	---------------

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Typical current consumption	0.8 A
-----------------------------	-------

TP105AT/733000 S00007 - Touch panel



2401408

<https://www.phoenixcontact.com/us/products/2401408>

Real-time clock

Realtime clock	Yes
----------------	-----

Supply

Power supply unit	24 V DC \pm 20 %
-------------------	--------------------

Mounting

Mounting type	Front mounting
---------------	----------------

Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back) NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	20 % ... 85 %

Dimensions

External dimensions

Width / Height / Depth	295 mm / 220 mm / 5 mm (Dimensions of the front plate)
------------------------	--

Installation dimensions

Width / Height / Installation depth	287 mm / 212 mm / 67 mm (Mounting cutout, depth with bus if bus system present in the device)
-------------------------------------	---

TP105AT/733000 S00007 - Touch panel



2401408

<https://www.phoenixcontact.com/us/products/2401408>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-15 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com