

IBS ISA SC/486DX/I-T - Termination board



2723945

<https://www.phoenixcontact.com/us/products/2723945>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Termination board with coprocessor with electrical isolation, incl. driver software and user manual on CD

Product description

INTERBUS Generation 4 coprocessor card

The IBS ISA SC/486DX/I-T provides the INTERBUS with a powerful PC controller board for high-level language programming of operator PCs in machines and plants. The control and automation programs run on the coprocessor of the IBS ISA SC/486DX/I-T. The PC system is thus free for the visualization of the process signals and parameters connected via INTERBUS.

The globally available PC/104 standard is used as a pluggable embedded PC board for the coprocessor of the IBS ISA SC/486DX/I-T. The control program is programmed with standard compilers such as Borland C or Microsoft C. The programs are developed and tested on the host PC and subsequently downloaded onto the coprocessor board.

There are 8 Mbyte IDE flash available as a local drive for the DOS operating system and the application. For runtime, the application can use the 640 kByte of the DOS operating system. The user-friendly high-level language interface (HLI) can be used for programming the application.

The power is normally supplied via the host PC. An external 5 V connection is available for a power supply independent of the host PC. A failure of the power supply to the host PC has no effect on the operation of the IBS ISA SC/486DX/I-T, the connected INTERBUS or the control program running on the coprocessor.

A built-in power supply unit for the PC ISA slot (24 V IN / 5 V OUT) IBS PC EXT PS/24DC/FIL can also be purchased as an accessory.

Commercial data

Item number	2723945
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DREABA
GTIN	4017918154134
Weight per piece (including packing)	479.2 g
Weight per piece (excluding packing)	479.2 g
Customs tariff number	84733020
Country of origin	DE

IBS ISA SC/486DX/I-T - Termination board



2723945

<https://www.phoenixcontact.com/us/products/2723945>

Technical data

Product properties

Product type	PLC controller board
Type	PC card
Format	1 deep slot, (222 x 99 x 35) mm, double slot width

System properties

Clock frequency	100 MHz
Retentive data storage	NVRAM
Operating system	Windows NT

Addressable areas

I/O	8 bytes, selectable between 100 and 3F8 (hex)
-----	---

INTERBUS-Master

Amount of process data	max. 4096 Byte (INTERBUS)
Number of devices with parameter channel	max. 62

Local diagnostics

Designation	READY/RUN, FAIL
Monitored function	INTERBUS
Optical representation	Status display via LED

System requirements

Configuration tool	CMD from version 4.5x
Diagnostics tool	DIAG+ from version 1.14
Driver	Windows NT

Electrical properties

Local diagnostics	READY/RUN, FAIL INTERBUS Status display via LED
	READY/RUN Coprocessor Status display via LED
	UL Power supply Status display via LED
Transmission medium	Copper
Maximum power dissipation for nominal condition	max. 12.5 W

Supply

Supply voltage	5 V DC
Supply voltage range	± 5 % (including ripple)
Power supply connection	Via ISA bus or ext. (2-pos. printed circuit board)
Typical current consumption	2.5 A

Interfaces

Interrupts	Selectable between IRQ 3, 5, 7, 9, 10, 11, 12, 15
------------	---

INTERBUS remote bus

IBS ISA SC/486DX/I-T - Termination board



2723945

<https://www.phoenixcontact.com/us/products/2723945>

Connection method	9-pos. D-SUB female connector (optionally optical fiber possible via interface converters) with electrical isolation
-------------------	--

Parameterization/operation/diagnostics

Connection method	RS-232-C, D-SUB 9-pos. male connector
-------------------	---------------------------------------

Host system

Connection method	IBM-compatible PCs with ISA slot, from 386 SX processor
-------------------	---

Dimensions

Width	229 mm
Height	107 mm
Depth	35 mm

External dimensions

Width / Height / Depth	229 mm / 107 mm / 35 mm
------------------------	-------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
----------------------	------

Mounting

Mounting type	In the host system
---------------	--------------------

IBS ISA SC/486DX/I-T - Termination board



2723945

<https://www.phoenixcontact.com/us/products/2723945>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com