

IB IL 24 PWR IN - Inline terminal

2726311

<https://www.phoenixcontact.com/us/products/2726311>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Inline power terminal block, without accessories, 24 V DC



The figure shows the version IB IL 24 PWR IN-PAC

Product description

The terminal is designed for use within an Inline station. It enables the 24 V supply voltage to be fed into the main circuit (U_M). In addition, this terminal can be used to supply power for a 24 V segment circuit (U_S).

Your advantages

- Segment circuit can be protected by an external fuse
- Main circuit protected by an external fuse
- Supply of the 24 V main voltage U_{M}
- Feed-in or provision of the 24 V segment voltage U_S

Commercial data

Item number	2726311
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR01
Product key	DRI121
GTIN	4017918168155
Weight per piece (including packing)	61.9 g
Weight per piece (excluding packing)	44 g
Customs tariff number	85389091
Country of origin	DE


IB IL 24 PWR IN - Inline terminal

2726311

<https://www.phoenixcontact.com/us/products/2726311>

Technical data

Dimensions

Dimensional drawing	
Width	12.2 mm
Height	119.8 mm
Depth	71.5 mm

Material specifications

Color	green
-------	-------

Interfaces

Inline local bus

Connection method	Inline data jumper
Transmission speed	500 kbps / 2 Mbps (Can be used in Inline stations with these transmission speeds)

System properties

Module

ID code (dec.)	none
ID code (hex)	none
Register length	0 bit
Required parameter data	0 Byte
Required configuration data	0 Byte

Product properties

Product type	I/O component
Product family	Inline
Type	modular Inline
Number of plugs	1

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Electrical properties

Test section	7.5 V supply (bus logics)/24 V supply (I/O) 500 V AC 50 Hz 1 min 24 V supply (I/O) / functional ground 500 V AC 50 Hz 1 min
--------------	--

IB IL 24 PWR IN - Inline terminal



2726311

<https://www.phoenixcontact.com/us/products/2726311>

Protective circuit	7.5 V supply (bus logic)/functional ground 500 V AC 50 Hz 1 min
	Surge protection; Suppressor diode
	Reverse polarity protection; Parallel polarity protection diode
	Overload protection, short-circuit protection in the segment circuit; No

Potentials: Main circuit supply (U_M)

Supply voltage	24 V DC (nominal value)
Supply voltage range	19.2 V ... 30 V (including all tolerances, including ripple)
Power supply	max. 8 A (sum of $U_M + U_S$)

Potentials: Segment circuit supply (U_S)

Supply voltage	24 V DC (nominal value)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Power supply	max. 8 A (sum of $U_M + U_S$)

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)

Mounting

Mounting type	DIN rail mounting
---------------	-------------------


IB IL 24 PWR IN - Inline terminal

2726311


<https://www.phoenixcontact.com/us/products/2726311>

Drawings

Dimensional drawing



Connection diagram




IB IL 24 PWR IN - Inline terminal

2726311

<https://www.phoenixcontact.com/us/products/2726311>



Block diagram



Internal wiring of the terminal points

IB IL 24 PWR IN - Inline terminal



2726311

<https://www.phoenixcontact.com/us/products/2726311>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com