

IB IL AI 8/SF - Inline terminal

2727831

<https://www.phoenixcontact.com/us/products/2727831>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline analog input terminal, without accessories, 8 inputs, 0 - 20 mA, 4 - 20 mA, ± 20 mA, 0 - 10 V, ± 10 V, (additionally 0 - 40 mA, ± 40 mA, 0 - 5 V, ± 5 V, 0 - 25 V, ± 25 V, 0 - 50 V), 2-conductor connection technology

Product description

The terminal is designed for use within an Inline station. It is used to acquire analog voltage and current signals.

Commercial data

Item number	2727831
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DRI141
GTIN	4017918818425
Weight per piece (including packing)	156.4 g
Weight per piece (excluding packing)	129.41 g
Customs tariff number	85389091
Country of origin	DE

IB IL AI 8/SF - Inline terminal

2727831

<https://www.phoenixcontact.com/us/products/2727831>

Technical data

Dimensions

Dimensional drawing	
Width	48.8 mm
Height	119.8 mm
Depth	71.5 mm

Material specifications

Color	green
-------	-------

Interfaces

Inline local bus

No. of channels	8
Connection method	Inline data jumper
Transmission speed	500 kbps
Transmission physics	Copper

System properties

Programming data

Length code (hex)	02
ID code (dec.)	95
Length code (dec)	02
Process data channel	32 bit
Input address area	4 Byte
Output address area	4 Byte
Parameter channel (PCP)	0 Byte
Register length (bus)	32 bit

Fieldbus data telegram

Required parameter data	6 Byte
-------------------------	--------

Input data

Analog: General

Input name	Analog inputs
Number of inputs	max. 8 (single ended)
A/D conversion time	approx. 10 µs

IB IL AI 8/SF - Inline terminal



2727831

<https://www.phoenixcontact.com/us/products/2727831>

Connection technology	2-conductor (shielded)
Current input signal	0 mA ... 20 mA
	4 mA ... 20 mA
	-20 mA ... 20 mA
	0 mA ... 40 mA
	-40 mA ... 40 mA
Voltage input signal	0 V ... 5 V
	-5 V ... 5 V
	0 V ... 10 V
	-10 V ... 10 V
	0 V ... 25 V
	-25 V ... 25 V
	0 V ... 50 V
Data formats	IB IL, IB ST, IB RT, standardized representation, PIO format
Limit frequency (3 dB)	3.5 kHz
Measuring principle	Successive approximation
Measured value resolution	16 bits (15 bits + sign bit)
Measured value representation	16 bit two's complement

Analog: Voltage inputs

Number of inputs	8 (Single-ended voltage inputs)
Voltage input signal	0 V ... 5 V
	-5 V ... 5 V
	0 V ... 10 V
	-10 V ... 10 V
	0 V ... 25 V
	-25 V ... 25 V
	0 V ... 50 V
Input resistance of voltage input	> 240 kΩ 0.01 %

Analog: Current inputs

Number of inputs	8 (single-ended current inputs)
Current input signal	0 mA ... 20 mA
	4 mA ... 20 mA
	-20 mA ... 20 mA
	0 mA ... 40 mA
	-40 mA ... 40 mA
Input resistance current input	25 Ω 0.01 %

Product properties

Product type	I/O component
Type	modular
	Inline

Electrical properties

Potentials: Communications power (U_L)

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 55 mA
	typ. 48 mA

Potentials: Supply of analog modules (U_{ANA})

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 35 mA
	typ. 30 mA

Electrical isolation/isolation of the voltage ranges

Test voltage: 5 V supply, incoming remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 5 V supply, outgoing remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 7.5 V supply (bus logic), 24 V supply U_{ANA} / I/O	500 V AC, 50 Hz, 1 min
Test voltage: 7.5 V supply (bus logic), 24 V supply U_{ANA} / functional ground	500 V AC, 50 Hz, 1 min
Test voltage: I/O/functional ground	500 V AC, 50 Hz, 1 min

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

IB IL AI 8/SF - Inline terminal

2727831

<https://www.phoenixcontact.com/us/products/2727831>



Mounting type	DIN rail mounting
---------------	-------------------


IB IL AI 8/SF - Inline terminal

2727831


<https://www.phoenixcontact.com/us/products/2727831>

Drawings

Dimensional drawing



Connection diagram



IB IL AI 8/SF - Inline terminal



2727831

<https://www.phoenixcontact.com/us/products/2727831>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com