

# IBS MC FLASH 2MB - Memory

2729389

<https://www.phoenixcontact.com/us/products/2729389>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Program and configuration memory, 2 Mbyte



## Your advantages

- Program and configuration memory, plug-in

## Commercial data

Item number	2729389
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR10
Product key	DRAAZA
GTIN	4017918170127
Weight per piece (including packing)	61.6 g
Weight per piece (excluding packing)	49.95 g
Customs tariff number	85235110
Country of origin	TW

# IBS MC FLASH 2MB - Memory

2729389

<https://www.phoenixcontact.com/us/products/2729389>



## Technical data

### Product properties

Product type	Storage medium
Set comprises	2719483 IBS PLC5 DSC SYSKIT
	2719496 IBS PLC5 DSC SYSKIT E
	2725930 IBS BA DSC SYSKIT
	2725927 IBS BA DSC SYSKIT E
	2721303 IBS S7 300 SYSKIT
	2721316 IBS S7 300 SYSKIT E
	2721361 IBS S7 400 SYSKIT E
	2721374 IBS S7 400 SYSKIT
	2740067 IBS S7 400 ETH SYSKIT
	2740070 IBS S7 400 ETH SYSKIT E
	2751373 IBS S5 DSC SYSKIT
	2751386 IBS S5 DSC SYSKIT E
Memory type	FLASH-EPROM
Memory size	2 Mbyte

### Electrical properties

Maximum power dissipation for nominal condition	0.45 W
---	--------

#### Supply

Supply voltage	5 V DC
Supply voltage range	4.5 V DC ... 5.5 V DC
Typical current consumption	typ. 90 mA

### Dimensions

Width	54 mm
Height	85.6 mm
Depth	3.3 mm

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

# IBS MC FLASH 2MB - Memory

2729389

<https://www.phoenixcontact.com/us/products/2729389>



## Classifications

### ECLASS

ECLASS-13.0

27242212

### ETIM

ETIM 9.0

EC000192

### UNSPSC

UNSPSC 21.0

32101600

# IBS MC FLASH 2MB - Memory



2729389

<https://www.phoenixcontact.com/us/products/2729389>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)