TP104AT/722000 S00003 - Touch panel

2401616

https://www.phoenixcontact.com/us/products/2401616

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Similar figure

Touch panel; 26.4 cm / 10.4"-TFT display (analog resistive (polyester)); 640 x 480 pixel(s) (VGA); 65536 colors; Processor: Arm9™, 200 MHz; Interfaces: 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45; Operating system: Windows® CE 5.0; Software: TSvisRT; PROFIBUS DP

Commercial data

Item number	2401616
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRCABB
GTIN	4055626289557
Weight per piece (including packing)	2,379 g
Weight per piece (excluding packing)	2,379 g
Country of origin	DE

Technical data

Product properties

Product type	Operator panel

Computer data

Processor	Arm9™, 200 MHz
Operating system	Windows® CE 5.0
RAM	64 MB SDRAM
	512 KB SRAM
Data storage system	NOR-Flash, 32 MB

Display

Display type	26.4 cm / 10.4"-TFT
Screen resolution	640 x 480 Pixel(s) (VGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	360 cd/m² typical (adjustable)
MTBF	50000 h
Color spectrum	65536 colors
Reading angle left	80.00 °
Reading angle right	80.00 °
Reading angle top	65.00 °
Reading angle bottom	80.00 °

Interfaces

Interfaces	2x USB Host 2.0
Optional interfaces	none
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	PROFIBUS DP

System properties

User software	TSvisRT

Electrical properties

Service life of battery	5 years (typical)

Supply

Power supply unit	24 V DC ±20 %
Typical current consumption	0.6 A

Real-time clock

Real-time clock	Yes

Mounting

Mounting type	Front mounting

Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
	NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Altitude	3000 m
Permissible humidity (operation)	20 % ... 85 %
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Dimensions

External dimensions

Width / Height / Depth	328 mm / 249 mm / 5 mm (Dimensions of the front plate)

Installation dimensions

Width / Height / Installation depth	303 mm / 222 mm / 67 mm (Mounting cutout, depth with bus if bus system present in the device)

Classifications

UNSPSC

UNSPSC 21.0	43211904

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(b), 6(b)-II, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com