


IBS RL 24 OC-LK-2MBD - Monitoring block

2732499

<https://www.phoenixcontact.com/us/products/2732499>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows version IBS RL 24 OC-LK

Repeater for signal monitoring and amplification for INTERBUS; fiber optic technology with 2 Mbaud, divides the system into segments and enables individual branches to be switched off during operation

Your advantages

- Rugged metal housing
- Comprehensive diagnostic functions
- M12 connector for I/O devices
- Rugged Line connector for INTERBUS, either with fiber optic or twisted pair, and supply voltage

Commercial data

Item number	2732499
Packing unit	1 pc
Sales key	DR03
Product key	DRI516
GTIN	4017918187095
Weight per piece (including packing)	712.7 g
Weight per piece (excluding packing)	640 g
Customs tariff number	85176200
Country of origin	DE

Technical data

Dimensions

Width	127 mm
Height	67 mm
Depth	71 mm

Interfaces

INTERBUS

Connection method	IP67-RL connector with FO connection
Transmission speed	2 Mbps

System properties

Programming data

Length code (hex)	0
ID code (dec.)	0C
Length code (dec)	0
Process data channel	0 bit
Input address area	0 Byte
Output address area	0 Byte
Parameter channel (PCP)	0 Byte
Register length (bus)	0 bit

Product properties

Product type	I/O component
Product family	Ruggedline
Type	Block design

Electrical properties

Supply: Module electronics

Supply voltage	24 V DC
Supply voltage range	18.5 V DC ... 32 V DC (including ripple)
Ripple	Max 3.6 V _{SS} within the permissible voltage range

Connection data

Connection method	Fiber optic
-------------------	-------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	0 °C ... 55 °C
Degree of protection	IP65/IP67
Air pressure (operation)	860 hPa ... 1080 hPa (up to 1500 m above sea level)

IBS RL 24 OC-LK-2MBD - Monitoring block



2732499

<https://www.phoenixcontact.com/us/products/2732499>

Air pressure (storage/transport)	660 hPa ... 1080 hPa (up to 3500 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	100 %
Permissible humidity (storage/transport)	95 % (non-condensing)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Air clearances and creepage distances

Air clearances and creepage distances	in accordance with EN 50178: 1998
---------------------------------------	-----------------------------------

Mounting

Mounting type	on mounting panel
	Panel mounting

IBS RL 24 OC-LK-2MBD - Monitoring block




2732499

<https://www.phoenixcontact.com/us/products/2732499>

Drawings

Connection diagram



IBS RL 24 OC-LK-2MBD - Monitoring block



2732499

<https://www.phoenixcontact.com/us/products/2732499>

Classifications

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

2732499

<https://www.phoenixcontact.com/us/products/2732499>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com