

PC WORX UA SERVER-PLC 10 - Driver and interface software



2402684

<https://www.phoenixcontact.com/us/products/2402684>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



OPC UA server for communication with a maximum of 10 modular small-scale controllers (AXC 1xxx or ILC 1x1)

Product description

The PC WORX UA SERVER provides the variables of controllers that have been programmed with PC Worx to all OPC UA clients. All variables are mapped in the server according to the PLCopen profile. The variable names are automatically synchronized from the current project. The server supports all security profiles via the binary profile, thereby enabling all access to be regulated.

A user-friendly configurator guides you through the configuration of controllers and security settings. Diagnostic information regarding active communication can also be displayed from another computer using the configurator.

Your advantages

- Safety configuration with support from tools
- Detailed diagnostic features
- Direct access to all data types, arrays, and complex structures supported by PC Worx.
- Transparent access to redundant controllers
- Standardized access according to the PLCopen information model for IEC 61131-3

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2402684 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | DR13 |
| Product key | DRDBAG |
| GTIN | 4055626119427 |
| Weight per piece (including packing) | 25.5 g |
| Weight per piece (excluding packing) | 25.5 g |
| Customs tariff number | 49119900 |
| Country of origin | DE |

PC WORX UA SERVER-PLC 10 - Driver and interface software



2402684

<https://www.phoenixcontact.com/us/products/2402684>

Technical data

Notes

General

| | |
|---|--|
| Information regarding the system requirements | Note the individual properties and requirements of the devices. Should you have any questions, please contact the Support team directly or the relevant contact person in Sales. |
| Information regarding the update rate | Guaranteed update rates greatly depend on the selected controller, the control capacity, and the selected PC. |

Product properties

| | |
|-----------------|---|
| Product type | Drivers and interfaces |
| Scope of supply | Packaging with license letter for single-user license (software via download) |

System properties

| | |
|-----------------------------------|---|
| Intended use for the software | Runtime license |
| Information regarding the version | Valid for Version 1.1 (for features of older versions, please refer to the version information in the download area) The versions of devices, other software packages or the operating system must be kept up to date. |

License information

| | |
|---|--|
| Type of license | Single-user license |
| Information regarding the type of license | License-free configurator. Server without license limited to one hour's runtime in demo mode |

Functionality

| | |
|---------------------------------|---|
| Basic functions | Data exchange according to DA profile spec 1.02 (2012) |
| | Security Policies: None, Basic128RSA15, Basic256 |
| | Message Security: Mode none, sign, sign&encrypt |
| | Communication profile according to the PC-based server via binary protocol using TCP/IP |
| | Easy access to arrays and structures |
| | Variable mapping according to PLCopen profile spec 1.00 |
| | Data exchange with up to 10 controllers |
| Integrated function | Analysis |
| | Data acquisition |
| | Communication |
| | Configuration |
| Supported controller | ILC 1xx |
| | AXC 1xxx |
| Number of supported controllers | max. 10 |
| Number of OPC items | max. 500 |
| Number of OPC items/controller | no limit, depends on the controller utilization |

PC WORX UA SERVER-PLC 10 - Driver and interface software



2402684

<https://www.phoenixcontact.com/us/products/2402684>

| | |
|-------------------------------------|--|
| | typ. 500 (for AXC 1xxx and ILC 1x1) |
| Supported data types (standard) | BOOL, BYTE, INT, DINT, UINT, SINT, USINT, UDINT, WORD, DWORD, REAL, LREAL, STRING, TIME according to IEC 61131 |
| Supported data types (user-defined) | ARRAY OF, STRUCTS, ARRAY OF STRUCT, STRUCT in STRUCT according to IEC 61131 |

System requirements

| | |
|-----------------------|-----------------------------------|
| Operating system | Windows® 7 (32-Bit/64-Bit) |
| | Windows® 8.1 (32-Bit/64-Bit) |
| | Windows® 10 (32-Bit/64-Bit) |
| | Windows® Server 2012 |
| | Windows® Server 2016 |
| Processor | min. Intel® Core™ i3-2100 (2 GHz) |
| Interfaces | min. Gigabit Ethernet |
| Languages supported | English |
| Software requirements | PC Worx Version 6 or later |

PC WORX UA SERVER-PLC 10 - Driver and interface software



2402684

<https://www.phoenixcontact.com/us/products/2402684>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27242504 |
| ECLASS-15.0 | 27242504 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002537 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43232400 |
|-------------|----------|

PC WORX UA SERVER-PLC 10 - Driver and interface software



2402684

<https://www.phoenixcontact.com/us/products/2402684>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.039 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com