

# PC WORX UA SERVER-PLC 10 - Driver and interface software



2402684

<https://www.phoenixcontact.com/us/products/2402684>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



OPC UA server for communication with a maximum of 10 modular small-scale controllers (AXC 1xxx or ILC 1x1)

## Product description

The PC WORX UA SERVER provides the variables of controllers that have been programmed with PC Worx to all OPC UA clients. All variables are mapped in the server according to the PLCopen profile. The variable names are automatically synchronized from the current project. The server supports all security profiles via the binary profile, thereby enabling all access to be regulated.

A user-friendly configurator guides you through the configuration of controllers and security settings. Diagnostic information regarding active communication can also be displayed from another computer using the configurator.

## Your advantages

- Safety configuration with support from tools
- Detailed diagnostic features
- Direct access to all data types, arrays, and complex structures supported by PC Worx.
- Transparent access to redundant controllers
- Standardized access according to the PLCopen information model for IEC 61131-3

## Commercial data

Item number	2402684
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR13
Product key	DRDBAG
GTIN	4055626119427
Weight per piece (including packing)	25.5 g
Weight per piece (excluding packing)	25.5 g
Customs tariff number	49119900
Country of origin	DE

# PC WORX UA SERVER-PLC 10 - Driver and interface software



2402684

<https://www.phoenixcontact.com/us/products/2402684>

## Technical data

### Notes

#### General

Information regarding the system requirements	Note the individual properties and requirements of the devices. Should you have any questions, please contact the Support team directly or the relevant contact person in Sales.
Information regarding the update rate	Guaranteed update rates greatly depend on the selected controller, the control capacity, and the selected PC.

### Product properties

Product type	Drivers and interfaces
Scope of supply	Packaging with license letter for single-user license (software via download)

### System properties

Intended use for the software	Runtime license
Information regarding the version	Valid for Version 1.1 (for features of older versions, please refer to the version information in the download area) The versions of devices, other software packages or the operating system must be kept up to date.

#### License information

Type of license	Single-user license
Information regarding the type of license	License-free configurator. Server without license limited to one hour's runtime in demo mode

#### Functionality

Basic functions	Data exchange according to DA profile spec 1.02 (2012)
	Security Policies: None, Basic128RSA15, Basic256
	Message Security: Mode none, sign, sign&encrypt
	Communication profile according to the PC-based server via binary protocol using TCP/IP
	Easy access to arrays and structures
	Variable mapping according to PLCopen profile spec 1.00
	Data exchange with up to 10 controllers
Integrated function	Analysis
	Data acquisition
	Communication
	Configuration
Supported controller	ILC 1xx
	AXC 1xxx
Number of supported controllers	max. 10
Number of OPC items	max. 500
Number of OPC items/controller	no limit, depends on the controller utilization

# PC WORX UA SERVER-PLC 10 - Driver and interface software



2402684

<https://www.phoenixcontact.com/us/products/2402684>

	typ. 500 (for AXC 1xxx and ILC 1x1)
Supported data types (standard)	BOOL, BYTE, INT, DINT, UINT, SINT, USINT, UDINT, WORD, DWORD, REAL, LREAL, STRING, TIME according to IEC 61131
Supported data types (user-defined)	ARRAY OF, STRUCTS, ARRAY OF STRUCT, STRUCT in STRUCT according to IEC 61131

## System requirements

Operating system	Windows® 7 (32-Bit/64-Bit)
	Windows® 8.1 (32-Bit/64-Bit)
	Windows® 10 (32-Bit/64-Bit)
	Windows® Server 2012
	Windows® Server 2016
Processor	min. Intel® Core™ i3-2100 (2 GHz)
Interfaces	min. Gigabit Ethernet
Languages supported	English
Software requirements	PC Worx Version 6 or later

# PC WORX UA SERVER-PLC 10 - Driver and interface software



2402684

<https://www.phoenixcontact.com/us/products/2402684>

## Classifications

### ECLASS

ECLASS-13.0	27242504
ECLASS-15.0	27242504

### ETIM

ETIM 10.0	EC002537
-----------	----------

### UNSPSC

UNSPSC 21.0	43232400
-------------	----------

# PC WORX UA SERVER-PLC 10 - Driver and interface software



2402684

<https://www.phoenixcontact.com/us/products/2402684>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.039 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)