

FLM DI 8 M8 - Distributed I/O device



2736929

<https://www.phoenixcontact.com/us/products/2736929>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The space-saving local bus device is particularly suitable for use in close proximity to the process. Functions: 8 digital inputs with 3 ms filter time, channel-specific diagnostics, short-circuit and overload protection, 600 mA nominal current, M8 connection method.

Product description

The device is designed for use in the Fieldline Modular M8 local bus, which is opened by a Fieldline or Inline bus coupler. It is used to acquire digital signals.

Commercial data

Item number	2736929
Packing unit	1 pc
Sales key	DR03
Product key	DRI431
GTIN	4046356076241
Weight per piece (including packing)	159.6 g
Weight per piece (excluding packing)	158.04 g
Customs tariff number	85389091
Country of origin	DE

FLM DI 8 M8 - Distributed I/O device



2736929

<https://www.phoenixcontact.com/us/products/2736929>

Technical data

Product properties

Type	modular
No. of channels	8

System properties

Module

ID code (dec.)	178
ID code (hex)	B2
Length code (hex)	81
Process data channel	8 bit
Input address area	8 bit
Output address area	0 bit
Register length	8 bit
Required parameter data	1 Byte

Electrical properties

Potentials

Voltage supply U_L	24 V DC
----------------------	---------

Supply: Module electronics

Connection method	M8 connector
Designation	U_L
Number of positions	4
Supply voltage	24 V DC
Supply voltage range	18 V DC ... 30 V DC (including ripple)
Supply current	3 A

Electrical isolation/isolation of the voltage ranges

Test voltage: To I/O	500 V AC
----------------------	----------

Input data

Digital:

Input name	Digital inputs
Description of the input	IEC 61131-2 type 1
Number of inputs	8
Connection method	M8 connector
Connection technology	2-, 3-conductor
Input voltage	24 V DC
Input voltage range "0" signal	-30 V DC ... 5 V DC
Input voltage range "1" signal	13 V DC ... 30 V DC
Nominal input voltage U_{IN}	24 V DC

FLM DI 8 M8 - Distributed I/O device



2736929

<https://www.phoenixcontact.com/us/products/2736929>


Total sensor current	max. 600 A
Filter time	3 ms
Protective circuit	Reverse polarity protection

Interfaces

Fieldline local bus

Connection method	2 M8 male connector
Designation connection point	Copper cable
Number of positions	4

Dimensions

Dimensional drawing	
Width	29.8 mm
Height	143 mm
Depth	26.5 mm
Drill hole spacing	133 mm
Note on dimensions	Length details incl. fixing clips

Material specifications

Color	green
-------	-------

Mechanical properties

Technical data

Drill hole spacing	133 mm
--------------------	--------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Degree of protection	IP65/IP67
Air pressure (operation)	80 kPa ... 106 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 %
Permissible humidity (storage/transport)	10 % ... 95 %

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

FLM DI 8 M8 - Distributed I/O device



2736929

<https://www.phoenixcontact.com/us/products/2736929>

Mounting

Mounting type

Panel mounting

FLM DI 8 M8 - Distributed I/O device




2736929

<https://www.phoenixcontact.com/us/products/2736929>


Drawings

Dimensional drawing



Side view (dimensions in mm)

Connection diagram



FLM DI 8 M8 - Distributed I/O device



2736929

<https://www.phoenixcontact.com/us/products/2736929>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com