

SD FLASH 2GB EMLOG - Program/configuration memory



2403484

<https://www.phoenixcontact.com/us/products/2403484>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Program and configuration memory for extending the internal Flash memory, plug-in, 2 GB, with license key and EMlog application, for use with an ILC 191 ME/AN Inline controller. The Emlog application is used to read from measuring devices via pulses, analog values, Modbus/RTU. The web-based interface can be used to configure the channels/devices and the connection to a higher-level system.

Product description

Program and configuration memory with EMLOG application program:

- Complete configuration and startup via integrated web interface (HTML 5)
- Maximum of 24 pulse inputs
- Maximum of 8 analog inputs for acquiring analog signals or measuring temperatures with resistance thermometers
- Connection of a maximum of 10 EMpro devices or up to 5 user-defined Modbus/RTU slaves
- Connection of a maximum of 10 IB IL PM 3P/N/EF-PAC Inline power measurement terminals
- Connection of a maximum of 30 power meters with M-Bus interface according to DIN EN 13757 (with restrictions)
- Forwarding of data to a management system via SQL server, OPC, Modbus/TCP, and CSV file

Your advantages

- License key for application program
- For storing application programs and other files in the file system of the PLC
- Required item: ILC 191 ME/AN, Order No. 2700074
- Program and configuration memory, plug-in, with license key and application program for reading from measuring devices
- Complete configuration and startup via integrated web interface (HTML 5)
- Max. 24 pulse inputs (with IB IL 24 DI8/HD-PAC)
- Forwarding of data to a management system via SQL server, OPC, Modbus/TCP, and CSV file
- Max. 10 EMpro EEM-MA250/400/600 energy measuring devices
- Max. 8 analog inputs (with IB IL AI 2/SF-PAC or IB IL TEMP 2 RTD-PAC)
- Max. 10 power measurement terminals (IB IL PM 3P/N/EF-PAC)
- Max. 30 power meters with M-Bus interface

Commercial data

Item number	2403484
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR10
Product key	DRAAZA
GTIN	4055626299174
Weight per piece (including packing)	9.2 g
Weight per piece (excluding packing)	8.5 g

SD FLASH 2GB EMLOG - Program/configuration memory



2403484

<https://www.phoenixcontact.com/us/products/2403484>

Customs tariff number	85235190
Country of origin	DE

SD FLASH 2GB EMLOG - Program/configuration memory



2403484

<https://www.phoenixcontact.com/us/products/2403484>

Technical data

Product properties

Product type	Storage medium
Application	Reading of measuring devices
Mounting position	vertical
Memory type	FLASH-EPROM
Memory size	2 GByte

Electrical properties

Maximum power dissipation for nominal condition	0.165 W
---	---------

Supply

Supply voltage	3.3 V DC
Supply voltage range	2.7 V DC ... 3.6 V DC
Typical current consumption	typ. 50 mA

Material specifications

Housing material	Plastic
------------------	---------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

Mounting

Mounting position	vertical
-------------------	----------

SD FLASH 2GB EMLOG - Program/configuration memory



2403484

<https://www.phoenixcontact.com/us/products/2403484>

Classifications

UNSPSC

UNSPSC 21.0	32101600
-------------	----------

SD FLASH 2GB EMLOG - Program/configuration memory



2403484

<https://www.phoenixcontact.com/us/products/2403484>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com