

FL BLUETOOTH AP - Wireless module



2737999

<https://www.phoenixcontact.com/us/products/2737999>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Factoryline Wireless Bluetooth Access Point, Bluetooth V2.0, 2.4 GHz frequency band, 1 wireless interface, WLAN-BlackChannelList, LEM, country approvals, IP20, COMBICON connection 9 - 30 V DC, RJ45 connection LAN, DSUB9-RS-232, SMA(f) antenna connection

Your advantages

- Protocol-transparent communication on Layer 2
- WLAN coexistence functions AFH, LEM, black channel listing
- Range* of up to 200 m
- Integrated special antenna (EPA)

Commercial data

Item number	2737999
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DNN2B1
GTIN	4046356042932
Weight per piece (including packing)	247.9 g
Weight per piece (excluding packing)	246.5 g
Customs tariff number	85176200
Country of origin	SE

FL BLUETOOTH AP - Wireless module



2737999

<https://www.phoenixcontact.com/us/products/2737999>

Technical data

Product properties

Product type	Wireless module
Type	Stand-alone

Wireless card

Number	1
Type	Bluetooth, 2.4 GHz ... 1 Mbps
Assembly note	Permanently installed

Electrical properties

Maximum power dissipation for nominal condition	4.8 W
---	-------

Supply: Module electronics

Connection method	Via COMBICON
Supply voltage	24 V DC
Supply voltage range	9 V DC ... 30 V DC
Supply current	200 mA
Current consumption	200 mA (at 24 V DC)

Interfaces

Ethernet

Interface	Ethernet
Number	1
Connection method	RJ45 jack

Antenna

Number	1
Connection method	SMA (male)

Functions

Operating modes	Access point / Ethernet client adapter / (COM server)
Configuration	Web-based management
Automatic channel selection	FHSS, AFH
Security	128-bit data encryption
	MAC filter
	Authentication
	PIN
	Non-discoverable
Wireless licenses	Europe, additional countries in the e-shop
Country support	Australia (Special rule: Please contact the Product Manager)
	Belgium
	Bulgaria
	Denmark

FL BLUETOOTH AP - Wireless module



2737999

<https://www.phoenixcontact.com/us/products/2737999>

	Germany
	Estonia
	Finland
	France
	Greece
	Great Britain
	Ireland
	Iceland
	Israel
	Italy
	Canada
	Latvia
	Liechtenstein
	Lithuania
	Luxembourg
	Malta
	Netherlands
	Norway
	Austria
	Poland
	Portugal
	Romania
	Russia (Special rule: Please contact the Product Manager)
	Sweden
	Switzerland
	Singapore
	Slovakia
	Slovenia
	Spain
	Czech Republic
	Turkey
	Hungary
	USA
	Cyprus (rep.)

Serial

Connection method	D-SUB 9 plug
Protocols supported	RS-232

Wireless

Designation	Bluetooth
Antenna connection method	SMA (female)
Frequency range	2.402 GHz ... 2.48 GHz (ISM bandwidth)
Frequency band	2.4 GHz
Wireless standard	Bluetooth 2.0

FL BLUETOOTH AP - Wireless module



2737999

<https://www.phoenixcontact.com/us/products/2737999>

Transmission power	max. 14 dBm (with automatic control)
Number of wireless interfaces	1
Wireless modules that can be connected	7
Profiles supported	LAP, PAN, SPP

Dimensions

Width	80 mm
Height	65 mm
Depth	25 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-30 °C ... 65 °C
Air pressure (operation)	795 hPa ... 1080 hPa (up to 2000 m above sea level)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 90 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	Panel mounting, optional DIN rail mounting
	Panel mounting
Assembly note	External OMNI antenna, antennas can be exchanged

FL BLUETOOTH AP - Wireless module



2737999

<https://www.phoenixcontact.com/us/products/2737999>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com